




Connectors > Automotive Connectors > Automotive Connector Accessories > Other Automotive Connector Accessories



Primary Product Color: **Black**

Automotive Connector Accessory Type: **Ferrite**

Operating Temperature Range: **-40 – 105 °C [-40 – 221 °F]**

Features

Product Type Features

Automotive Connector Accessory Type	Ferrite
-------------------------------------	---------

Body Features

Primary Product Color	Black
-----------------------	-------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Method	Bag
Packaging Quantity	1000

Other

Serviceable	Yes
-------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free


Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 2420610-1
CHERY CX62D AKI 90D PIGTAIL




TE Part # 1-353380-7
SQUIB CONN RETAINER ASSY 2P



TE Part # 2237024-1
REAR DOOR RHS/LHS SEATBELT CABLE ASSY



TE Part # 353378-7
SQUIB CONN HSG YELLOW



TE Part # 2420610-2
CHERY CX62D AKI 90D PIGTAIL


Also in the Series | AMP Auto Squib Products



Automotive Connector Caps & Covers (2)



Automotive Housings(12)




Automotive Terminals(1)



Connector Contacts(1)



Other Automotive Connector Accessories(19)



PCB Headers & Receptacles(1)



Power Contacts(1)

Customers Also Bought



TE Part #1612121-5
SQUIB 2POS PLUG HSG




TE Part #1674936-5
0.64 III RCPT NON SEALED TIN (S)



TE Part #CAT-T319-CH8172
TH/.025 CONNECTOR SYSTEM, HOUSING



TE Part #1612124-8
1DIA SOCKET AU



TE Part #1473139-1
SQUIB 11DIA MK-2 PLUG HSG



TE Part #1827120-1
SQUIB LOCKING BUTTON



TE Part #1565963-2
040III TAB NON SEALED AU



TE Part #1801764-1
FUSES AND RELAYS HOLDER, 36 MINIFUSES V2



TE Part #1801618-1
RELAY 40A HOLDER

Documents

Product Drawings
SQUIB CONN FERRITE

Japanese

CAD Files
Customer View Model
ENG_CVM_353379-2_A1.3d_igs.zip

English
Customer View Model



[ENG_CVM_353379-2_A1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_353379-2_A1.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English

Squib Connector

English

Instruction Sheet (non U.S.)

Japanese

Instruction Sheet (non U.S.)

Japanese

11dia squib connector checker

Japanese

Instruction Sheet (non U.S.)

Japanese