



Connectors > Terminal Blocks & Strips > Modular Terminal Blocks



Modular Terminal Block Product Type: **Screw Clamp Terminal Block**

Block Function: **Feed-Through**

Primary Product Color: **Gray**

Product Spacing: **8 mm [.315 in]**

Number of Positions: **2**

Features

Product Type Features

Modular Terminal Block Product Type	Screw Clamp Terminal Block
-------------------------------------	----------------------------

Configuration Features

Number of Levels	1
Gauge Type	A5-B5
Number of Circuits	1
Block Function	Feed-Through
Number of Positions	2

Electrical Characteristics

Power Loss	1.8 W
Operating Voltage Rating (UL & CSA) (Max) - Main Circuit	600 V
Impulse Withstanding Voltage Rating (IEC)	8000 V
Current Rating (IEC)	57 A
Current Rating (UL)	42 A
Current Rating (CSA)	42 A



Dielectric Withstanding Voltage (Max)	2200 V
Voltage Rating (IEC)	1000 V
Voltage Rating (CSA)	600 V
Short-Time Withstanding Current Rating @ 1s	1200 A
Operating Voltage	600 VAC

Body Features

Product Weight	14.1 g[.555 oz]
Primary Product Color	Gray

Termination Features

Termination Method to Wire & Cable	Screw Terminal
------------------------------------	----------------

Mechanical Attachment

DIN Rail Mounting Type	TH35-15, TH35-7.5
Connector Mounting Type	DIN Rail

Housing Features

Housing Material	Polyamide
------------------	-----------

Dimensions

Product Depth	47.3 mm[1.862 in]
Tool Size	4 mm[.157 in]
Wire Stripping Length	12 mm[.472 in]
Main Circuit Capacity - 2 Rigid Stranded Conductors per Screw Clamp	20 – 12 AWG
Main Circuit Capacity - Twin Ferrule per Screw Clamp	20 – 12 AWG
Main Circuit Capacity - 2 Flexible Conductors per Screw Clamp	20 – 12 AWG
Main Circuit Capacity - 1 Rigid Stranded Conductor per Screw Clamp	24 – 6 AWG
Main Circuit Capacity - 1 Non-Insulated Ferrule per Screw Clamp	.5 – 10 mm²
Main Circuit Capacity - 1 Insulated Ferrule per Screw Clamp	.5 – 6 mm²
Main Circuit Capacity - 1 Flexible Conductor per Screw Clamp	24 – 6 AWG
Product Length	47.3 mm[1.86 in]
Product Height	53 mm[2.087 in]
Product Spacing	8 mm[.315 in]
Wire Size	6 AWG

Usage Conditions



Installation Temperature Range	-5 – 40 °C[23 – 104 °F]
Operating Temperature Range	-55 – 110 °C[-67 – 230 °F]

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

IP Rating	IP20
UL Flammability Rating	UL 94V-0

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1SNK900201R0000
TC5-R1



TE Part # 1SNA174300R1700
PR3.Z2



TE Part # 1SNK505910R0000
ES4



TE Part # 1SNK908302R0000
JB8-2



TE Part # 1SNK900203R0000
TP2




TE Part # 1SNK900620R0000
PL8



TE Part # 1SNK908304R0000
JB8-4



TE Part # 1SNK900205R0000
TP4




TE Part # 1SNA164800R0300
PR3.G2



TE Part # 1SNK908310R0000
JB8-10



TE Part # 1SNK169999R0000
MC812PA




TE Part # 1SNK900624R0000
KCO




TE Part # 1SNK908305R0000
JB8-5



TE Part # 1SNK900603R0000
JB85-3




TE Part # 1SNA168700R2200
PR5



TE Part # 1SNK160004R0000
MC812-YL




TE Part # 1SNK908303R0000
JB8-3



TE Part # 1SNK160000R0000
MC812




TE Part # 1SNK900101R0000
CS



TE Part # 1SNA168500R1200
PR4


Also in the Series | **ENTRELEC SNK**



Modular Terminal Blocks(319)



Terminal Block & Strip Conducting Accessories(67)



Terminal Block & Strip Insulating Accessories(31)

Customers Also Bought



TE Part #1SNK510020R0000
ZS16-BL



TE Part #1SNK516010R0000
ZS35



TE Part #1SNK505010R0000
ZS4



TE Part #1SNK516150R0000
ZS35-PE



TE Part #1SNK510150R0000
ZS16-PE



TE Part #1SNK505910R0000
ES4



TE Part #1SET411019R0000
WD-1-DP-GR6080



TE Part #1SNK506010R0000
ZS6



TE Part #1SNK522010R0000
ZS70



TE Part #1SET111027R0000
WF007-08-GR

Documents

CAD Files

Customer View Model

ENG_CVM_CVM_1SNK508010R0000_A1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1SNK508010R0000_A1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_1SNK508010R0000_A1.2d_dxf.zip

1SNK508010R0000

Screw Clamp Terminal Block, Feed-Through, Gray, 8 mm [.315 in] Spacing, 2 Position,
Screw Terminal, Power & Signal, DIN Rail, 600 VAC, ENTRELEC SNK



English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ZS10

English

SNK SERIES TERMINAL BLOCKS

English

ENTRELEC Terminal Blocks Catalogue (RUS)

ENTRELEC Terminal Block - Master Catalog

ENTRELEC Terminal Block - Master Catalog

English

Essential Entrelec Terminal Blocks

French

Essential Entrelec Terminal Blocks

English

Essential Entrelec Terminal Blocks

Japanese

Agency Approvals

ZK-ZS_ATEX_1SND225112U1006-C-TE

English