

## ÖLFLEX® HEAT 180 H05SS-F EWKF

Europe-wide standardised silicone connection cables with increased mechanical performance

ÖLFLEX® HEAT 180 H05SS-F EWKF - silicone power cable according to type H05SS-F, for use in machines, plant construction and toolbuilding, suitable for +180°C

### Info

International use in combination with proven EWKF quality



UV-resistant



Temperature-resistant



Halogen-free



Cold-resistant

### Benefits

Harmonised use in Europe

Notch and tear-resistant silicone compounds reduce damage due to mechanical stress

For harsh environments, more durable than conventional H05SS-F standardised cables

Flexibility simplifies installation where space is limited

Possesses insulating properties after combustion due to remaining SiO<sub>2</sub> ash on the conductor

## ÖLFLEX® HEAT 180 H05SS-F EWKF

### Application range

Areas with high ambient temperatures and occasionally mechanical stress

Typical fields of application

- Steel, ceramic and iron works
- Bakery equipment and industrial furnaces
- Electric motor industry
- Sauna/solarium construction
- Thermal and heating elements
- Lighting technology
- Ventilator engineering
- Air-conditioning technology
- Galvanisation technology

### Product features

EWKF:

Initial tear propagation and notch resistance

Halogen-free (IEC 60754-1), no corrosive gases (IEC 60754-2), flame-retardant (IEC 60332-1-2)

Good hydrolysis and UV-resistance

Resistant to a multitude of oils, alcohols, vegetable and animal fats and chemical substances

Adequate ventilation must be ensured, since the mechanical properties of silicone cables decrease from +100°C in the absence of air

### Norm references / Approvals

EN 50525-2-83 (H05SS-F)

### Product Make-up

Fine-wire, tinned-copper conductor

Core insulation: based on EWKF silicone

Cores twisted together

Outer sheath: silicone-based EWKF, notch-resistant, black

### Technical Data

Classification:	ETIM 5.0 Class-ID: EC001578 ETIM 5.0 Class-Description: Flexible cable
Core identification code:	Colours according to VDE 0293-308, refer to Appendix T9
Conductor stranding:	Fine wire according to VDE 0295 Class 5/ IEC 60228 Class 5
Minimum bending radius:	Occasional flexing: 15 x outer diameter Fixed installation: 4 x outer diameter
Nominal voltage:	U0/U: 300/500 V
Test voltage:	2000 V
Protective conductor:	G = with GN-YE protective conductor X = without protective conductor
Temperature range:	-50 °C to +180 °C (adequate ventilation required)

## ÖLFLEX® HEAT 180 H05SS-F EWKF

### Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: [www.lappkabel.de/en/cable-standardlengths](http://www.lappkabel.de/en/cable-standardlengths)

Packaging size: coil  $\leq$  30 kg or  $\leq$  250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**ÖLFLEX® HEAT 180 H05SS-F EWKF**

Article number	Number of cores and mm <sup>2</sup> per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
ÖLFLEX® HEAT 180 H05SS-F EWKF				
0046900	2 X 0.75	6.4	14.4	54
0046901	3 G 0.75	7	21.6	67
00469023	4 G 0.75	7.6	28.8	87
00469033	5 G 0.75	8.5	36	105
0046904	2 X 1	6.8	19.2	63
0046905	3 G 1	7.2	28.8	81
00469063	4 G 1	7.9	38.4	98
00469073	5 G 1	8.8	48	121
0046908	2 X 1.5	8.4	28.8	84
0046909	3 G 1.5	8.9	43.2	103
00469103	4 G 1.5	9.9	57.6	128
00469113	5 G 1.5	10.9	72	154
0046912	2 X 2.5	9.8	48	141
0046913	3 G 2.5	10.4	72	158
00469143	4 G 2.5	11.6	96	195
00469153	5 G 2.5	12.9	120	241
0046916	3 G 4	12.3	115.2	239
00469173	4 G 4	13.7	153.6	312
0046919	3 G 6	14	172.8	345
00469203	4 G 6	15.6	230.4	451

Last Update (18.09.2017)

©2017 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03\_16