


FEATURES

- Easy-peel temperature strips for added convenience
- Non-reversible colour changing indication for easy identification
- Bracketed temperatures to suit specific applications

RS PRO Non-Reversible Temperature Sensitive Label, 138°C to 154°C, 4 Levels

RS Stock No.: 286-131



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Temperature Sensitive Labels



Product Description

Brought to you by the trusted RS PRO brand, these temperature-sensitive labels are micro-sized for easy application in electronics. The self-adhesive labels change colour when exposed to different temperatures, and so are a reliable way to easily indicate the exposed temperature of the product. These temperature levels indicate the exposed temperature at four different levels, and so will permanently record the highest bracketed temperature that the label, and so the product it was attached to, was exposed to. They can adhere securely to many types of surface, and so they are suitable for a variety of applications where temperature control is a concern.

General Specifications

Number of Temperature Levels	4	
Orientation	Circle	
Reversibility	Irreversible	
Shelf Life	24 months Polyester Acrylic	
Surface or carrier		
Adhesive Type		
Colour Change Material	Non-toxic, white crystalline, adhered with acrylic adhesive	
Tolerance	±1.5°C	
Covering Film	Polyester	
Storage	Store in a room temperature	
Pressure sensitive	No	
Applications	Food Industry, Pharmaceuticals, Medical products, Industrial equipment, Shipping and packaging for sensitive goods	

Mechanical Specifications

Dimensions	11mm X 4mm
Label Length	11mm
Label Width	11mm



Operation Environment Specifications

Minimum Temperature Sensitivity	138°C
Maximum Temperature Sensitivity	154°C

Approvals

Compliance/Certifications	RoHS Certificate of compliance

Accessories

Item Name	Item Description	Quantity
Time indicator label	Time Strip Non reversible time indicator label, 19 x40mm 3 months	1box of 100
Time indicator label	Time Strip Non reversible time indicator label 19 x40mm 6 months	1box of 100
Time indicator label	Time Strip Non reversible time indicator label 19 x40mm 12months	1box of 100
Time indicator label	Time Strip Non reversible time indicator label 19 x40mm 1month	1box of 100



Temperature Sensitive Labels



Physical Properties:

(Not for specification purposes)

	Low Temperatures	Mid Temperatures	High Temperatures
	(171ºC and below)	(177°C to 210°C)	(210ºC+)
Adhesive Type	Acrylic	Modified Acrylic	Modified Acrylic
Carrier	Polyester	Tissue	Tissue
Covering Film	Polyester	Kaladex	Polyimide
Colour Change Material	Non-toxic, white crystalline solid on a black absorbent backing, adhered with acrylic adhesive $29 \text{ to } 99^{\circ}\text{C} = \pm 1^{\circ}\text{C}$, $100 \text{ to } 154^{\circ}\text{C} = \pm 1.5^{\circ}\text{C}$ and $160 \text{ to } 280^{\circ}\text{C} = \pm 1\% + 1^{\circ}\text{C}$ Temperatures from $29 - 34^{\circ}\text{C} / 84 - 93^{\circ}\text{F} = 6$ months storage life, providing they are stored in a		
Tolerance			
Shelf Life			
	refrigerator inside a sealed bag.		
	Temperatures from 37 – 49°C / 99 – 120°F = 12 months storage life, providing they are stored		
	in a refrigerator inside a sealed bag.		
	Temperatures from 54 – 290º / 130 – 554ºF = 24 months storage life, store at room temperature & Humidity (i.e. 20ºC/68ºF & 50% relative humidity)		

RS Order Code	Description	Temperatures	Dimensions
286080	4 Level Micro Range 1	40-46°C	4mm x 11mm
286096	4 Level Micro Range 2	49-65ºC	4mm x 11mm
286103	4 Level Micro Range 3	71-88ºC	4mm x 11mm
286119	4 Level Micro Range 4	93-110ºC	4mm x 11mm
286125	4 Level Micro Range 5	116-132ºC	4mm x 11mm
286131	4 Level Micro Range 6	138-154ºC	4mm x 11mm