

Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: LED2WORK GmbH.

Supplier's address: Vertrieb, Stuttgarter Straße 13A, 75179 Pforzheim, DE

Model identifier: 2941-5021-00-LE-215e

Type of light source:

| | | | |
|---|------|---------------------------------|----------------------------|
| Lighting technology used: | LED | Non-directional or directional: | DLS |
| Light source cap-type (or other electric interface) | - | | |
| Mains or non-mains: | NMLS | Connected light source (CLS): | No |
| Colour-tuneable light source: | No | Envelope: | - |
| High luminance light source: | No | | |
| Anti-glare shield: | No | Dimmable: | Only with specific dimmers |

Product parameters

| Parameter | Value | Parameter | Value |
|-----------|-------|-----------|-------|
|-----------|-------|-----------|-------|

General product parameters:


| | | | |
|--|-------------------------|--|---|
| Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer | 5 | Energy efficiency class | C |
| Useful luminous flux (ϕ_{use}), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°) | 818 in Wide cone (120°) | Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set | 5 700 |
| On-mode power (P_{on}), expressed in W | 5,3 | Standby power (P_{sb}), expressed in W and rounded to the second decimal | 0,00 |
| Networked standby power (P_{net}) for CLS, expressed in W and rounded to the second decimal | - | Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set | 95 |
| Outer dimensions without separate control gear, light- | Height | 6 | Spectral power distribution in the range 250 nm to 800 nm, at full-load |
| | Width | 215 | |
| | Depth | 14 | |
| | | | See image in last page |

| | | | |
|---|-----|--|----------------|
| ing control parts and non-lighting control parts, if any (millimetre) | | | |
| Claim of equivalent power ^(a) | - | If yes, equivalent power (W) | - |
| | | Chromaticity coordinates (x and y) | 0,326 0,352 |
| Parameters for directional light sources: | | | |
| Peak luminous intensity (cd) | 453 | Beam angle in degrees, or the range of beam angles that can be set | 112 |
| Parameters for LED and OLED light sources: | | | |
| R9 colour rendering index value | 90 | Survival factor | - |
| the lumen maintenance factor | - | | |

(a) : not applicable;

(b) : not applicable;

Spektrale Strahlungsverteilung
Spectral power distribution



Model placed on the Union market from 22/11/2024



EPREL registration number: 2192510

<https://eprel.ec.europa.eu/qr/2192510>

Supplier: LED2WORK GmbH (Manufacturer)

Website: led2work.com

Customer care service:

Name: Vertrieb

Website: www.led2work.com

Email: info@led2work.com

Phone: +49 7231 44920-00

Address:

Stuttgarter Straße 13A

75179 Pforzheim

Germany