




Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Number of Positions: 3

Terminal Block Connector Type: Plug

Connector System: Wire-to-Board

Centerline (Pitch): 3.5 mm [.138 in]

Number of Rows: 1

Features

Product Type Features

Wire Protection	With
Terminal Block Connector Type	Plug
Connector System	Wire-to-Board

Configuration Features

Stacking Configuration	Side Stackable
Number of Positions	3
Number of Rows	1
Wire Entry Angle	45°
Wire Entry Location	Side

Electrical Characteristics

Operating Voltage	150 VAC
-------------------	---------

Body Features

Primary Product Color	Green
Lever Color	Orange



Product Orientation	Vertical
---------------------	----------

Contact Features

Contact Underplating Material	Nickel
Contact Mating Area Plating Material	Tin (Sn)
Contact Base Material	Stainless Steel
Contact Current Rating (Max)	2 A

Termination Features

Termination Method to Wire & Cable	Push-in, Spring Terminal
------------------------------------	--------------------------

Housing Features

Housing Material	PA 66
Centerline (Pitch)	3.5 mm[.138 in]

Dimensions

Wire Size	20 – 16 AWG
-----------	-------------

Usage Conditions

Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Quantity	200
--------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1986717-3
HEADER, 3P, 3.5mm 12.5 H



TE Part # 1986718-3
HEADER, 3P, 3.5 PCB 16.5 H WB


Customers Also Bought




TE Part #350389-1
.140 DIA PIN 20-14 PTPBR L/P



TE Part #3-1879355-8
RR03 5% 150K AMMO



TE Part #1546307-2
2P .374" DR BARRIER,W/WASHER



TE Part #1-350347-0
03P .140 MNL CAP PM NAT



TE Part #2-1462039-9
IM23GR=IM RELAY 50mW 5V




TE Part #1-640457-2
12P MTA100 HDR ASSY SQ R/A F/L



TE Part #1393243-4
RTE24012



TE Part #1-1419106-9
27E487=SOCKET,K10,8,SCW,PHEN, SURF-MNT



Documents

Product Drawings

Flush Mt Plug Spring Conn 3P 3.50mm

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1986716-3_A_c-1986716-3-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1986716-3_A_c-1986716-3-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1986716-3_A_c-1986716-3-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

5-1773463-2_Flush Mount Spring Type Plug

English

Agency Approvals

UL

English