



Identification & Labeling > Pre-Printed Markers > STD Snap-On Markers



Marker Style: **Snap-On**
Marker Size: **STD 02**
Compatible Cable Diameter Range: **1.4 – 1.8 mm [.055 – .071 in]**
Primary Product Color: **Yellow**
Marker Cut: **Straight**

[All STD Snap-On Markers \(957\)](#)

Features

Body Features

Marker Style	Snap-On
Marker Size	STD 02
Primary Product Color	Yellow
Primary Product Material	Polyoxymethylene

Dimensions

Compatible Cable Diameter Range	1.4 – 1.8 mm[.055 – .071 in]
---------------------------------	------------------------------

Printer/Label Features

Marker Cut	Straight
Marking Details	/

Packaging Features

Packaging Method	Strip
Packaging Quantity	300

Other

Printed Marking Color	Black
-----------------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 003324-000

STD02W-B

Also in the Series | Agastat 7000

A white rectangular AC relay with multiple green and gold pins on the bottom and a black terminal on the side.

AC Relays(8)

A collection of pre-printed markers, including a long orange one with a yellow label 'K' and a small yellow one with a black 'K'.

Pre-Printed Markers(957)

A black rectangular time delay relay with a black knob on top and several pins on the bottom.

Time Delay Relays(41)

Customers Also Bought

A black and grey 12-pin connector plug.

TE Part #207017-1
METRIMATE PLUG, 12 POS

A black 2-pin connector plug.

TE Part #1-480318-0
02P CMNL PLUG HSG F/H NATL

A black 2-pin connector plug with a locking mechanism.

TE Part #1011-255-0205
BKSHL, 2P, BLK, PLG,ST,SR,NW6/7.5/8.5/10

Three different colored (blue, green, black) wedge-shaped locking components.

TE Part #CAT-D487-W416
Wedgelocks: DEUTSCH DT 5/10

A grey 4-pin connector plug with a red locking tab.

TE Part #DT06-4S
PLG, 4P, GRY, N

A long yellow pre-printed marker with a black label.

TE Part #CAT-T3437-ST2999
STD Snap-On Markers

A collection of various colored pre-printed markers.

TE Part #8-1768043-7
STD06W/SA

Documents

Product Drawings

STD02Y-SLASH

English

Datasheets & Catalog Pages

STD/STB-type Snap-on Pre-printed Wire & Cable Markers

English

IDENTIFICATION SELECTION GUIDE

English

STD and STB Technical Datasheet

English

Product Specifications

RW-2538 STD and STB work instruction

English