


Product datasheet

Specifications



Retrofit connection, Tesys Deca Advanced, for 3P LC1D115-150A contactor

LAD9150RFT

EAN Code: 3606487159407

Main

Range of product	TeSys Deca
Range	TeSys
Device short name	LAD9
Product or component type	Terminal extension
Poles description	3P
Product compatibility	LC1D115 LC1D150
Quantity per set	1

Complementary

Product weight	0.43 kg
----------------	---------

Environmental

Ambient air temperature for operation	-40...70 °C
Ambient air temperature for storage	-60...80 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6 cm
Package 1 Width	9 cm
Package 1 Length	9.4 cm
Package 1 Weight	452 g
Unit Type of Package 2	S02
Number of Units in Package 2	20
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	9.655 kg

Contractual warranty

Warranty (in months)	18
----------------------	----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
SCIP Number	608af421-265e-4dfd-b0b3-1192c9364536
EU RoHS Directive	Compliant By Exemption
REACH Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer

Lifetime extension	
Repair	No

Use Again

Repack and remanufacture	
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative

