



LOC	DIST	REVISONS				
		P	LTR	DESCRIPTION	DATE	DWN I APVD
AD	00	W3	REVISED	PER ECO-11-004587	11MAR11	RK HMR

D



"AMP", PART NO. & DATE CODE
MARKED (WHITE) 1.58±0.38 [.062±.015] HIGH CHARS.
IN AREA SHOWN WHEN HOUSING SIZE PERMITS



CAVITY IDENT. MARKED (WHITE)
1.17±0.38 [.046±.015] HIGH CHARS. SECOND AND
EVERY FIFTH CAVITY, ONE SIDE.




SEE DETAIL Z




BASIC DIMENSION FOR
ODD NUMBER OF SPACES
(SEE THE TABLE)

BASIC DIMENSION FOR
EVEN NUMBER OF SPACES
(SEE THE TABLE)

DETAIL Z



SECTION X-X



SECTION Y-Y ROTATED 90° CLOCKWISE

- 2 SEE TABLE FOR NUMBER OF DETENTS. DETENT ON THIS SIDE FOR HOUSINGS WITH ONE DETENT.
- 3 STRAIN RELIEF LOCATORS WILL APPEAR ON 20 POSITION AND LARGER HOUSINGS.
- 4 USE EXTRACTION TOOL 91052-1 TO REMOVE RECEPTACLE CONTACTS.
- 5 THESE HOUSINGS ARE COMPATIBLE WITH ANY MOD II SHROUDED HEADER.
- 6 HOUSINGS WILL ACCOMMODATE ALL MOD IV, IV.5 AND MOD V CONTACTS.
- 7 MATERIAL: FLAME RETARDANT GLASS FILLED NYLON, COLOR: BLACK PER ASTM D4066.
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

8	OBSOLETE	ALL	2	81.28	[3.200]	31	64	6-87631-6
		NONE	2	81.28	[3.200]	31	64	6-87631-5
8	OBSOLETE	ALL	2	73.66	[2.900]	28	58	6-87631-4
		NONE	2	73.66	[2.900]	28	58	6-87631-3
		-	-	-	-	-	-	6-87631-2
		-	-	-	-	-	-	-
8	OBSOLETE	ALL	2	60.96	[2.400]	23	48	6-87631-0
		NONE	2	60.96	[2.400]	23	48	5-87631-9
8	OBSOLETE	ALL	2	88.90	[3.500]	35	72	5-87631-8
		NONE	2	88.90	[3.500]	35	72	5-87631-7
8	OBSOLETE	ALL	2	88.90	[3.500]	34	70	5-87631-6
		NONE	2	88.90	[3.500]	34	70	5-87631-5
8	OBSOLETE	ALL	2	83.82	[3.300]	32	66	5-87631-4
		NONE	2	83.82	[3.300]	32	66	5-87631-3
		ALL	2	76.20	[3.000]	29	60	5-87631-2
		NONE	2	76.20	[3.000]	29	60	5-87631-1
		-	-	-	-	-	-	5-87631-0
		-	-	-	-	-	-	-
		-	-	-	-	-	-	4-87631-8
		-	-	-	-	-	-	-
8	OBSOLETE	ALL	2	68.58	[2.700]	26	54	4-87631-6
		NONE	2	68.58	[2.700]	26	54	4-87631-5
		ALL	2	66.04	[2.600]	25	52	4-87631-4
		NONE	2	66.04	[2.600]	25	52	4-87631-3
		ALL	2	63.50	[2.500]	24	50	4-87631-2
		NONE	2	63.50	[2.500]	24	50	4-87631-1
		ALL	2	55.88	[2.200]	21	44	4-87631-0
		NONE	2	55.88	[2.200]	21	44	3-87631-9
8	OBSOLETE	ALL	2	53.34	[2.100]	20	42	3-87631-8
		NONE	2	53.34	[2.100]	20	42	3-87631-7
		ALL	2	50.80	[2.000]	19	40	3-87631-6
		NONE	2	50.80	[2.000]	19	40	3-87631-5
		ALL	2	48.26	[1.900]	18	38	3-87631-4
		NONE	2	48.26	[1.900]	18	38	3-87631-3
		ALL	2	45.72	[1.800]	17	36	3-87631-2
		NONE	2	45.72	[1.800]	17	36	3-87631-1
		ALL	2	43.18	[1.700]	16	34	3-87631-0
		NONE	2	43.18	[1.700]	16	34	2-87631-9
		ALL	2	40.64	[1.600]	15	32	2-87631-8
		NONE	2	40.64	[1.600]	15	32	2-87631-7
		ALL	2	38.10	[1.500]	14	30	2-87631-6
		NONE	2	38.10	[1.500]	14	30	2-87631-5
		ALL	2	35.56	[1.400]	13	28	2-87631-4
		NONE	2	35.56	[1.400]	13	28	2-87631-3
		ALL	2	33.02	[1.300]	12	26	2-87631-2
		NONE	2	33.02	[1.300]	12	26	2-87631-1
		ALL	2	30.48	[1.200]	11	24	2-87631-0
		NONE	2	30.48	[1.200]	11	24	1-87631-9
		ALL	2	27.94	[1.100]	10	22	1-87631-8
		NONE	2	27.94	[1.100]	10	22	1-87631-7
		ALL	2	25.40	[1.000]	9	20	1-87631-6
		NONE	2	25.40	[1.000]	9	20	1-87631-5
		ALL	1	22.86	[.900]	8	18	1-87631-4
		NONE	1	22.86	[.900]	8	18	1-87631-3
		ALL	1	20.32	[.800]	7	16	1-87631-2
		NONE	1	20.32	[.800]	7	16	1-87631-1
		ALL	1	17.78	[.700]	6	14	1-87631-0
		NONE	1	17.78	[.700]	6	14	87631-9
		ALL	1	15.24	[.600]	5	12	87631-8
		NONE	1	15.24	[.600]	5	12	87631-7
		ALL	1	12.70	[.500]	4	10	87631-6
		NONE	1	12.70	[.500]	4	10	87631-5
		ALL	1	10.16	[.400]	3	8	87631-4
		NONE	1	10.16	[.400]	3	8	87631-3
		ALL	1	7.62	[.300]	2	6	87631-2
		NONE	1	7.62	[.300]	2	6	87631-1
	MARKING	NO. OF DETENTS	D	NO. OF SPACES	NO. OF POSN	PART NUMBER		