

## Features

- Good tensile strength and surface quality
- User – friendly for both home and office environments
- Due to the low shrinkage, PLA will not deform after cooling
- Minimal thermal tension
- Minimal deformation

## RS PRO 3D Printing Materials

RS Stock No.: 0360160



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

*This product is perfect for all kind of projects, from prototypes and models to decorative and functional parts.*

## General Specifications

Printing Technology	FDM
Printing Material	PLA
Machine Specific	No
Colour	White
For Use With	Common Desktop 3D Printers
Material Type	PLA
Print Speed	>250 mm/s for 0.2mm layer height
Bed Prep	PEI tape is the ideal build surface

## Mechanical Specifications

Diameter	1.75 mm
Weight	1 kg
Specific gravity	1,24 g/cc
MFI	6 g/10 min
Tensile Strength	45 Mpa
Tensile Modulus	3500 Mpa
Impact Strength	< 5 KJ/m <sup>2</sup>
Tolerance	± 0.05mm
Roundness	≥ 95%
Spool size	20cm (D) x 47mm (h) & Hub diameter 52mm
Ovality Tolerance (Max)	± 5%

**Operation Environment Specifications**

Printing Temperature	190 – 230 °C
Melting Temperature	155 °C ± 10 °C
Glass Transition Temperature	55 - 60 °C
Storage Temperature	15-25°C

**Approvals**

Compliance/Certifications	IEC / CE / CSA
Declarations	MFR Declaration of Conformity