



Main

Range of product	EZD
Product or component type	Voltage release
Device short name	SHT

Complementary

Voltage release type	Shunt trip release
[Uc] control circuit voltage	24 V DC
Threshold tripping voltage	0.7 Un tripping
Supply holding power	35 W
Mounting mode	Internal mounting
Response time	50 ms
Auxiliary connection terminal	Screw terminal 1.5 mm ²

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0910 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations