



Top Handle Chainsaw XGT®

UC003G

40Vmax • 24,8 m/s • 30 cm / 12"

Powerful XGT® Chainsaw with high chain speed for demanding applications.

XGT® Battery powered Chainsaw which delivers high chainspeed for fast cutting. It also has a main power switch with auto power-off function for better battery saving and avoiding unintentional start-up.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Max. Chain Speed (No Load)	24,8 m/s
chain bar length	300 mm (12")
Chain Pitch	0,325 / 3/8 "
Chain Gauge	0,043 / 0,050 "
Chain Gauge	1,1 / 1,3 mm
Number of Drive Links	51 / 46
Chain Oil Tank	200 ml
Brushless Motor	✓
Vibration Level, Cutting Wood	5,0 m/s ²
Vibration Uncertainty (K Factor), Cutting Wood	1,5 m/s ²
Sound Pressure Level (L _{pA})	93 dB(A)
Sound Power Level (L _{WA})	101 dB(A)

User benefits

- Lightweight for reduced operator fatigue
- Large oil filling port with view window allows operator to easily add and check bar oil level
- Main power switch with auto power-off function for battery saving and avoiding unintentional start up
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Adjustable automatic chain lubrication with large oil reservoir
- Captive nuts to prevent loss of nuts when replacing guide bar or saw chain

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing