


Technical data



5310NRZZG15

Double row angular contact ball bearings



Double row angular contact ball bearing, polyamide cage, snap ring and groove on outer diameter, shield on both sides

VISUAL (S)



5310NRZZG15

Double row angular contact ball bearings

PRODUCT DEFINITION

Brand	SNR
d - Internal diameter	50 mm
D - External diameter	110 mm
B - Bearing/Inner ring width	44,4 mm
d1 - External diameter inner ring	68 mm
D1 - Inner diameter outer ring	96,1 mm
a - Charge load application point	55 mm
- Contact angle	25 °
a min - Min position Groove	3,07 mm
a max - Max position groove	3,28 mm
rs - Min fillet radius	2 mm
rNs - Min fillet radius	0,6 mm
D3 - Max bottom groove diameter	106,81 mm
b min - Min groove width	2,7 mm
b max - Max groove width	3 mm
r0 max - Max bottom groove radius	0,6 mm
D4 max - Max outer diameter of assembled stop ring	116,6 mm
f - Stop ring thickness	2,41 mm
Snap ring reference	R 110
Radial clearance class	CN
Precision class	P0
Mass	1,6 kg



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

5310NRZZG15

Double row angular contact ball bearings

PRODUCT PERFORMANCE

C - Dynamic load	78400000 mN
C0 - Static load	61600000 mN
Cu - Fatigue limit load	38000000 mN
f0 - Coefficient	13.9
N ref - Reference thermal speed	31200 °/s
N lim - Mechanical Limit Speed	28800 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

BEARING FREQUENCIES

BPFO - Over rolling frequency on outer ring (60 rpm)	3.196 Hz
BPFI - Over rolling frequency on inner (60 rpm)	4.804 Hz
BSF - Over rolling frequency on rolling element (60 rpm)	4.328 Hz
BRF - Rotational frequency - rolling element (60 rpm)	2.164 Hz
FTF - Rotational frequency - cage (60 rpm)	0.4 Hz

ABUTMENT

da min - Min shoulder diameter IR	59 mm
da max - Max shoulder diameter IR	68 mm
Da max - Max shoulder diameter OR	101 mm
Ca min - Mini segment position	5,43 mm
Ca max - Max segment position	5,74 mm
ra max - Max shaft & housing fillet radius	2 mm
rNa max - Max fillet radius on segment side	0,6 mm
Db min - Min stop ring position diameter	118 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15