

D-SCE-1K-12-50-4

✓ ACTIVE

TE Internal #: 372389-000

Ladder, Fluid Resistant, 3:1, Yellow, 1 Markers per Sleeve, 50 mm [2 in] Length, 12.7 mm [.5 in] Expanded Inside, Printable Tubing

[View on TE.com >](#)



Identification & Labeling > Printable Tubing > D-SCE Fluid Resistant Sleeves



Printable Tubing Type: **Ladder**
Printable Tubing Grade: **Fluid Resistant**
Shrink Ratio: **3:1**
Primary Product Color: **Yellow**
Markers per Sleeve: **1**

[All D-SCE Fluid Resistant Sleeves \(65\)](#)

Features

Product Type Features

Printable Tubing Type	Ladder
Printable Tubing Grade	Fluid Resistant

Body Features

Shrink Ratio	3:1
Primary Product Color	Yellow
Markers per Sleeve	1

Dimensions

Product Length	50 mm[2 in]
Expanded Inside Diameter (Min)	12.7 mm[.5 in]
Recovered Inside Diameter (Max)	4.2 mm[.17 in]
Compatible Cable Diameter Range	4.6 – 10.7 mm[.183 – .425 in]

Usage Conditions

Operating Temperature Range	-75 – 135 °C[-103 – 275 °F]
-----------------------------	-----------------------------

Printer/Label Features

Printer Technology	Thermal Transfer
--------------------	------------------

Packaging Features

Packaging Quantity	1000
--------------------	------



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 311292-000
TMS-RJS-RIBBON-4DSCE



TE Part # 1-2186501-1
T3212-SWARE-PRINTER



TE Part # F55931-000
1966-RIBBON



TE Part # 1-2186500-1
T3212-PRINTER





TE Part # 1-2186502-1
T3224-PRINTER



TE Part # 1-2186503-1
T3224-SWARE-PRINTER

Customers Also Bought




TE Part #D18609-000
B-155-07-F



TE Part #621060-000
D-142-56




TE Part #CAT-T3437-D1
D-SCE Fluid Resistant Sleeves



TE Part #9-160463-5
FASTON, PGYBCK, PIDG, PH BR, .250, 16-14



TE Part #661315-000
B-150-07-F



TE Part #1SNS420895Z0000
100631116-- (ENT14627 A)

Documents

Datasheets & Catalog Pages

IDENTIFICATION SELECTION GUIDE

English

D-SCE Heat Shrink Identification Sleeves

English

Product Specifications

Product Specification

English

IDENTIFCATION PRINTER PRODUCT RIBBON MATRIX

English

Instruction Sheets

Instruction Sheet (non U.S.)

English