






























## 8790 HMA Zyklop 1/4" socket



**Application:** Hexagon headed bolts, screws and nuts

**Design:** Manual and (non-impact) machine applications, ball intercept ring, knurls at base for precision handling in manual operations, chrome vanadium, brushed chrome-plated finish.  
Take it easy toolfinder: Colour coding to enable the desired socket to be easily located.

							
	mm	mm	mm	mm	mm	mm	
05003501001		4,0	23,0	6,9	13,0	10,0	
05003502001		4,5	23,0	7,5	13,0	10,0	
05003503001		5,0	23,0	8,2	13,0	10,0	
05003504001		5,5	23,0	8,8	13,0	10,0	
05003505001		6,0	23,0	9,4	13,0	10,0	
05003506001		7,0	23,0	11,0	13,0	10,0	
05003507001		8,0	23,0	12,0	13,0	10,0	
05003508001		9,0	23,0	13,0	14,0	10,0	
05003509001		10,0	23,0	14,5	14,5	-	
05003510001		11,0	23,0	16,0	15,0	13,0	
05003511001		12,0	23,0	17,0	16,0	13,0	
05003512001		13,0	23,0	18,0	17,0	13,0	
05003513001		14,0	23,0	20,0	18,0	13,0	
05003514001			$\frac{3}{16}$ "	23,0	7,5	13,0	10,0
05003515001			$\frac{7}{32}$ "	23,0	8,8	13,0	10,0
05003516001			$\frac{1}{4}$ "	23,0	11,0	13,0	10,0
05003517001			$\frac{9}{32}$ "	23,0	11,0	13,0	10,0
05003518001			$\frac{5}{16}$ "	23,0	12,0	13,0	10,0
05003519001			$\frac{11}{32}$ "	23,0	13,0	14,0	10,0
05003520001			$\frac{3}{8}$ "	23,0	14,5	14,5	-
05003521001			$\frac{7}{16}$ "	23,0	16,0	15,0	13,0
05003522001			$\frac{1}{2}$ "	23,0	18,0	17,0	13,0
05003523001			$\frac{9}{16}$ "	23,0	20,0	18,0	13,0