




TE Internal #: 1658744-3
SFP, Cage Assembly, Signal, Operating Temperature Range -55 – 85 °C [-67 – 185 °F], Data Rate (Max) 4 Gb/s, 4 Ports, Port Matrix Configuration 1 x 4
[View on TE.com >](#)

Connectors > Pluggable IO Connectors & Cages



Form Factor: **SFP**
Pluggable I/O Product Type: **Cage Assembly**
Sealable: **No**
Circuit Application: **Signal**
Operating Temperature Range: **-55 – 85 °C [-67 – 185 °F]**

Features

Product Type Features

Cage Type	Ganged
Form Factor	SFP
Pluggable I/O Product Type	Cage Assembly
Sealable	No

Configuration Features

Number of Ports	4
Port Matrix Configuration	1 x 4

Electrical Characteristics

Data Rate (Max)	4 Gb/s
-----------------	--------

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
---------------------------	--------------------------

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application



Pluggable I/O Applications	SFP
Circuit Application	Signal
Other	
Included Lightpipe	No
EMI Containment Feature Type	Internal/External EMI Springs

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 1367147-1
SFP COVER, UNPLATED



TE Part # 2185239-4
ASSY, SEATING TOOL, SFP+



TE Part # 1367147-3
SFP COVER, UNPL, NO LOGO



TE Part # 1761394-1
DUST COVER, SFP, GANGED & STACKED

Customers Also Bought




TE Part #2-338309-2
9P.HDP20 PLUG ASSY



TE Part #454949-E
M12 FEMALE, D CODE, 4P, 17MM SMT



TE Part #1888371-1
MJ,2X1RJ45+2USB,BLACK,NOLEDS



TE Part #1623804-8
SQZ10 3R3 5% WIRE



TE Part #CAT-T3437-W919
WP White Polyester Labels




TE Part #2358986-1
SFP+ 1x1 Cage Assembly, Thermal Bridge



TE Part #254152-E
M12 METAL SHELL, FEMALE, VERT, 9MM

TE Part #5-1768423-3
LBG-U-03446/1/EET-0585/PE271



TE Part #4-1879378-8
TLR3A 3.0W R002 1% 2K RL 20K MOQ

Documents

Product Drawings
SFP 1X4 CAGE ASSY
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1658744-3_F.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1658744-3_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1658744-3_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English