



## M18 FUEL 8kg SDS Max Drilling & Breaking Hammer

M18 FHM-0CO



- The M18 FHM is the most productive SDS-Max tool MILWAUKEE have produced, delivering AC style power with the flexibility of the cordless M18 platform
- Next generation POWERSTATE brushless motor: This is MILWAUKEE's most powerful motor utilising higher grade magnets and 175% more copper vs previous motors
- Next generation REDLINK PLUS intelligence system delivers an advanced digital overload protection for tool and battery and uniquely enhances the tool performance under load

### MODEL VARIANT



### INCLUDES

- M18 FHM-0 (1)
- Grease Tube (1)
- Side Handle (1)
- Hard Case (1)

**Categories:** Concrete Drilling & Demolition

## PRODUCT SPECIFICATIONS

Battery platform	M18 REDLITHIUM-ION HIGH OUTPUT
Voltage (V)	18
FUEL Gauge	Yes
LED Light	Yes
No Load Speed (rpm)	0 - 380
Tool Reception	SDS Max
Blow energy (J)	11
Max. drilling concrete (mm)	45
Max. drilling core bit (mm)	150
Max. drilling tunnel bit (mm)	65
Optimised drilling capacity in concrete (mm)	16 - 38
Max. hammer rate (bpm)	0 - 2900
Weight with battery pack if applicable (kg)	10.4 (12.0Ah)