


APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-25 °C TO +85 °C	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C
	VOLTAGE	AC 250 V , DC 350 V		
	CURRENT	10 A	APPLICABLE CABLE	φ15
SPECIFICATIONS				
ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.		X	X
ELECTRIC CHARACTERISTICS				
CONTACT RESISTANCE	CONTACT SHALL BE MEASURED AT DC 1 A	5 mΩ MAX.	X	X
INSULATION RESISTANCE	500 V DC.	1000 MΩ MIN.	X	X
VOLTAGE PROOF	1000 V AC. FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	X
MECHANICAL CHARACTERISTICS				
CONTACT INSERTION AND WITHDRAWAL FORCES	φ1.57±0.003 BY STEEL GAUGE.	INSERTION AND WITHDRAWAL FORCES : 0.5 N MIN.	X	-
CONNECTOR INSERTION AND WITHDRAWAL FORCES	MEASURED BY APPLICABLE CONNECTOR.	INSERTION AND WITHDRAWAL FORCES LOCKING DEVICE WITH UNLOCK : 45 N MAX. LOCKING DEVICE WITH LOCK : - N MAX.	X	-
MECHANICAL OPERATION	500 TIMES INSERTIONS AND EXTRACTIONS.	CONTACT RESISTANCE: 5 mΩ MAX.	X	-
VIBRATION	FREQUENCY: 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, — m/s ² AT 2h, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	X	-
SHOCK	490 m/s ² DIRECTIONS OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	X	-
ENVIRONMENTAL CHARACTERISTICS				
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 °C, 90 TO 95 %, 96 h.	① INSULATION RESISTANCE: 10 MΩ MIN (AT HIGH HUMIDITY). ② INSULATION RESISTANCE: 100 MΩ MIN (AT DRY). ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	-
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -40 → R/T ⁽¹⁾ → +100 → R/T °C TIME 30 → 10 TO 15 → 30 → 10 TO 15 min UNDER 5 CYCLES.	① INSULATION RESISTANCE: 1000 MΩ MIN. . ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	-
CORROSION SALT MIST	EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.	NO HEAVY CORROSION RUIN THE FUNCTION.	X	-
DRY HEAT	EXPOSED AT + 100 °C , 96 h.	NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	-
COLD	EXPOSED AT - 40 °C , 96 h.	NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	-
RESISTANCE TO SOLDERING HEAT	SOLDER TEMPERATURE, +380±10°C ,FOR IMMERSION DURATION, 30 ⁺¹ s.	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	X	-
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, +350±10°C FOR IMMERSION DURATION, 2 TO 3 s.	SOLDER SURFACE TO BE FREE FROM PIN-HOLE, NO WETTING AND OTHER DEFECTS.	X	-
COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
0				
REMARK		APPROVED	MO. SATOH	06.12.19
NOTE (1) R/T : ROOM TEMPERATURE		CHECKED	MO. SATOH	06.12.19
		DESIGNED	DS. MATSUNE	06.12.19
Unless otherwise specified, refer to JIS C 5402.		DRAWN	MK. SATO	06.12.06
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELG4-025492-00	
HRS	SPECIFICATION SHEET	PART NO.	JR21JK-10S	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL114-0545-2-00	 1/1