



Image may differ from product. See specification for details.



TMMP 2X170

Standard jaw puller, 2 armed

One of the most common ways to dismount small to medium size bearings is to use a mechanical puller. The SKF TMMP 2X170 is a two arm puller for small to medium bearings. The SKF Standard Jaw Pullers TMMP series allow for easy and fast dismounting jobs and safe puller operation.

- Cone system for automatic centring and secure positioning of arms
- Strong springs keep arms apart for easy operation
- Hardened, high quality carbon steel

Overview

Dimensions

Width of grip external	25 – 170 mm
Effective arm length	135 mm
Claw height	9 mm
Claw length	12 mm
Claw width	21 mm
Spindle head, hexagon size	19
Total spindle length	251 mm

Properties

Recommended applications	For the dismantling of bearings, gears, pulleys and other industrial ring shaped components in industrial, construction and agricultural applications with an interference fit on the shaft
Suitable for workpiece dismantling from a Cylindrical seating (straight shaft)	Yes
Suitable for bearing dismantling from a Tapered seating (conical shaft)	Yes
Suitable for bearing dismantling from a Sleeve (adapter or withdrawal sleeve)	Yes
Suitable for workpiece dismantling from a Blind arrangement (housing with shaft)	No
Suitable for workpiece dismantling from a Housing	No
Suitable for bearing type(s)	All
Dismantling force generation	Spindle
Special features	Cone-system for automatic centring and locking of the arms
Number of arms	2
Pulling force (max)	18 kN
Spindle torque (max)	40 N·m
Spindle nose piece	No
Colour	Black
Material	Alloy engineering steels, hardened and tempered
Coating	Chemical blackened
Content	1x Puller TMMP 2x170 1x Printed instructions for use

Logistics

Product net weight	2.1 kg
--------------------	--------

eClass code	23-05-19-01
UNSPSC code	27111712

Compatible products

Spare part

Spare spindle for Standard jaw puller	TMMP 2X170-6
---------------------------------------	------------------------------

Accessory

Extremely high viscosity bearing grease with solid lubricants	LGEV 2/0.035
Puller protection blanket	TMMX 210

Recommended product

Standard jaw puller, 2 armed	TMMP 2X65
Standard jaw puller, 3 armed	TMMP 3X185
Standard jaw puller, 3 armed	TMMP 3X230
Standard jaw puller, 3 armed	TMMP 3X300



Terms of use

By accessing and using this website / app owned and published by AB SKF (publ.) (556007-3495 · Gothenburg) ("SKF"), you agree to the following terms and conditions:

Warranty Disclaimer and Limitation of Liability

Although every care has been taken to assure the accuracy of the information on this website / app, SKF provides this information "AS IS" and DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. You acknowledge that your use of this website / app is at your sole risk, that you assume full responsibility for all costs associated with use of this website / app, and that SKF shall not be liable for any direct, incidental, consequential, or indirect damages of any kind arising out of your access to, or use of the information or software made available on this website / app.

Any warranties and representations in this website / app for SKF products or services that you purchase or use will be subject to the agreed upon terms and conditions in the contract for such product or service.

Further, for non-SKF websites / apps that are referenced in our website / app or where a hyperlink appears, SKF makes no warranties concerning the accuracy or reliability of the information in these websites / apps and assumes no responsibility for material created or published by third parties contained therein. In addition, SKF does not warrant that this website / app or these other linked websites / apps are free from viruses or other harmful elements.

Third Party Services

When viewing YouTube content via the SKF website(s) (i.e. using [YouTube API Services](#)), you agree to be bound by the [YouTube Terms of Service](#).

Copyright

Copyright in this website / app copyright of the information and software made available on this website / app rest with SKF or its licensors. All rights are reserved. All licensed material will reference the licensor that has granted SKF the right to use the material. The information and software made available on this website / app may not be reproduced, duplicated, copied, transferred, distributed, stored, modified, downloaded or otherwise exploited for any commercial use without the prior written approval of SKF. However, it may be reproduced, stored and downloaded for use by individuals without prior written approval of SKF. Under no circumstances may this information or software be supplied to third parties.

This website /app includes certain images used under license from Shutterstock, Inc.

Trademarks and Patents

All trademarks, brand names, and corporate logos displayed on the website / app are the property of SKF or its licensors, and may not be used in any way without prior written approval by SKF. All licensed trademarks published on this website / app reference the licensor that has granted SKF the right to use the trademark. Access to this website / app does not grant to the user any license under any patents owned by or licensed to SKF.

Changes

SKF reserves the right to make changes or additions to this website / app at any time.