



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Pb (13% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought



TE Part #207398-7
MMATE PIN HDR ASSY, 10P LF




TE Part #213740-1
SIZE 8 PIN CONT ASY, 10 AWG



TE Part #2-1445085-4
micro mnl hdr assy s/row au lf



TE Part #2-1445085-6
micro mnl hdr assy s/row au lf



TE Part #3-1617072-6
3SBC1538A2 = M39016/13-073L



TE Part #1-1617110-9
JMGST-5MW = M28776/7-007M



TE Part #1617148-6
JMGAPD-5L = M39016/18-025L



TE Part #2098269-1
10P Plug Assembly (2x5), Gener



TE Part #6-2176312-7
RP 1E 0.1W 60K4 0.1% 25PPM 1K RL



TE Part #5222132-1
JACK, VERTICAL, PCB, 75 OHM, BNC

Documents

Product Drawings

[UMNL II SOK SN/AUNI/PHBZ LP](#)

English

CAD Files

Customer View Model

[ENG_CVM_770249-4_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_770249-4_E.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_770249-4_E.2d_dxf.zip](#)

English

[3D PDF](#)

English

[3D PDF](#)



3D

Customer View Model

[ENG_CVM_CVM_770249-4_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_770249-4_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_770249-4_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY](#)

English

Product Specifications

[Application Specification](#)

English