



Connectors > RF Connectors > Coax Connectors



RF Interface: **BNC**

RF Connector Style: **Jack**

RF Connector Mated Outer Diameter (Approximate): **14.53 mm [.572 in]**

Impedance: **50 Ω**

RF Connector Coupling Mechanism: **Bayonet**

Features

Product Type Features

RF Interface	BNC
RF Connector Style	Jack
Connector System	Cable-to-Board, Cable-to-Panel
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	1
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Body Material	Zinc
Body Plating Material	Nickel

Contact Features

RF Connector Center Contact Underplating Material	Nickel
---	--------



	30 µin
RF Connector Center Contact Plating Material	Gold (Au)
RF Connector Center Contact Material	Phosphor Bronze

Termination Features

Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	3.43 mm[.135 in]

Mechanical Attachment

Panel Mount Feature Type	Lockwasher and Nut
PCB Mount Retention	With
RF Connector Coupling Mechanism	Bayonet
Connector Mounting Type	Panel Mount
RF Contact Captivation Method	Mechanical
Detent	With

Dimensions

Mounting Post Length	4.01 mm[.158 in]
Profile Height from PCB	13.18 mm[.519 in]
RF Connector Mated Outer Diameter (Approximate)	14.53 mm[.572 in]

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Operating Frequency	1 GHz
---------------------	-------

Packaging Features

Packaging Method	Tube
------------------	------

Other

Grade	Commercial
Dielectric Material	Polymethylpentene

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold




EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-076-BNCJKISG50 BNC RF Connector: Jack Assembly, Isolated Ground Protection, 50 Ohm	 TE Part # 5227079-7 COMM. BNC-PLUG	 TE Part # 5221128-1 PLUG,COMMERCIAL BNC	 TE Part # 1-5227079-1 COMM BNC PLUG
 TE Part # CAT-076-BNCJKSH50 BNC RF Connector: jack assembly - short, 50 Ohm, 4Ghz	 TE Part # 5413771-3 JACK BLKHD,COML BNC,HEX CRIMP	 TE Part # 5227079-6 COMM. BNC-PLUG	 TE Part # 1-5221128-0 PLUG,COMMERCIAL BNC



TE Part # 5413779-3
COML BNC,50 OHM, HEX CRIMP



TE Part # 1-221128-0
PLUG,COMMERCIAL BNC



TE Part # 1-5227079-6
COMM BNC PLUG



TE Part # 5227169-7
BNC SOLDER JACK RECEPTACLE



TE Part # 1-5221128-7
PLUG,COMMERCIAL BNC



TE Part # 5413959-3
BNC HEX RT ANG PLUG 50 OHM



TE Part # 2-5221128-3
PLUG,COMMERCIAL BNC



TE Part # 413779-3
COML BNC,50 OHM, HEX CRIMP



TE Part # 8-5227079-2
COMM BNC PLUG



TE Part # 2-221128-3
PLUG,COMMERCIAL BNC



TE Part # 5227169-5
BNC - SOLDER RECEPT



TE Part # 5227079-5
COMM BNC PLUG

Customers Also Bought




TE Part #6609104-7
PE0SSSX0=C1132




TE Part #2176056-3
RLP73V 2B R012 5% 5K RL



TE Part #354308-E
DRCBTB 1,27 50 M BTB22 20,2 137 * 094 TR



TE Part #124044-E
SMCB 26 F AB VV 6-03 CLHD * H007 137 E00




TE Part #8-1879133-3
RN 0603 6K34 0.1% 10PPM 1K RL




TE Part #8-1879265-9
RP 2B 280K 0.1% 15PPM 1K RL



TE Part #4-2176366-5
RQ 0603 1K24 0.1% 10PPM 1K RL



TE Part #1-100317-5
DUAL LOADED



Documents

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_5413515-2_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_5413515-2_C.3d_igs.zip

English

Customer View Model

ENG_CVM_5413515-2_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Decoupled Connectors

English

Product Specifications

PCB Decoupled BNC Straight & Right Angle Jacks

English

Product Specification

English

Agency Approvals

UL Report

English