

FEATURES

- Valves do not require a minimum operating pressure and have a high operating pressure as indicated
- Valve operation is not affected by mounting position
- The solenoid valves satisfy all relevant EC directives

GENERAL

Differential pressure

See «SPECIFICATIONS» [1 bar = 100 kPa]

Maximum viscosity

65 cSt (mm²/s)

Response time

5 - 25 ms

fluids (*)	temperature range (TS)	seal materials (*)
air, inert gas, water, oil	- 20°C to + 90°C - 20°C to + 40°C	NBR (nitrile) UR (cast urethane)

MATERIALS IN CONTACT WITH FLUID

(*) Ensure that the compatibility of the fluids in contact with the materials is verified

Body	Brass
Core tube	Stainless steel
Core and plugnut	Stainless steel
Springs	Stainless steel
Seat	Brass
Seals	NBR
Disc	NBR or UR
Disc holder (NO function)	PA
Shading coil	Copper

ELECTRICAL CHARACTERISTICS

Coil insulation class

F

Connector

Spade plug (cable Ø 6-10 mm)

Connector specification

ISO 4400 / EN 175301-803, form A

Electrical safety

IEC 335

Electrical enclosure protection

Moulded IP65 (EN 60529)

Standard voltages

DC (=) : 24V - 48V

(Other voltages and 60 Hz on request)


AC (~) : 24V - 48V - 115V - 230V / 50 Hz

prefix option	power ratings				operator ambient temperature range (TS)	replacement coil		type ⁽¹⁾
	inrush ~	holding ~		hot/cold =		~	=	
	(VA)	(VA)	(W)	(W)		(C°)	230 V/50 Hz	
SC	34	15,6	6	7 / 9,7	-20 to + 75	400325-117	400325-142	01
	30	22,5	9	9,5/15,3	-20 to + 50	400325-217	400325-242	01
	55	23	10,5	9/11,2	-20 to + 75	400425-117	400425-142	02
	78	35	16,7	-	-20 to + 50	400425-217	-	02
	-	-	-	14/19,7	-20 to + 25	-	400425-342	02

(1) Refer to the dimensional drawings on the following page.

SPECIFICATIONS

pipe size	orifice size	flow coefficient Kv		min.	operating pressure differential (bar)						power coil (W)		catalogue number	options				
					max. (PS)									maintained man. operator	FPM	EPDM	CR	PTFE
					air (*)		water (*)		oil (*)									
G	(mm)	(m³/h)	(l/min)		~	=	~	=	~	=		~/=						
NC - Normally closed, NBR seals and disc																		
1/4	1,2	0,05	0,8	0	50	35	50	35	35	35	6	9,7	SCG262C019	-	V	E	J	T
	2,4	0,17	2,8	0	25	10	25	8	11	8	6	9,7	SCG262C020	-	V	E	J	T
					35	15	35	10	20	10	9	15,3	SCG262C021	-	V	E	J	T
	3,2	0,3	5	0	9	4	11	4	6	4	6	9,7	SCG262C022	MO	V	E	J	T
					15	7	16	6	11	6	9	15,3	SCG262C023	MO	V	E	J	T
					20	5	20	4	13	4	10,5	11,2	SCG262D232	MO	V	E	J	T
	4	0,43	7,2	0	12	2,5	13	2,5	10	3	10,5	11,2	SCG262C202	MO	V	E	J	T
					6,5	1,7	6,5	1,7	6,5	1,7	10,5	11,2	SCG262C208	MO	V	E	J	T
	5,6	0,73	12,2	0	2,5	1,2	3,0	1,3	2,5	1,3	6	9,7	SCG262C013	MO	V	E	J	T
					1,8	1	2,5	1	1,9	1	6	9,7	SCG262C090	MO	V	E	J	T
					4	1,2	5	1	4	1,2	10,5	11,2	SCG262C210	MO	V	E	J	T
					6	1,7	6,5	1,3	6	1,3	16,7	19,7	SCG262B212	-	V	E	J	T
NC - Normally closed, NBR seals and UR disc																		
1/4	1,2	0,05	0,8	0	100	32	100	32	75	30	10,5	11,2	SCG262D200	MO	-	-	-	T
NO - Normally open, NBR seals and disc																		
1/4	3,2	0,3	5	0	9	5,5	7	4	6,5	4	10,5	11,2	SCG262A262	-	V	E	J	T
	4	0,43	7,2	0	5,5	3	5	2	4	2	10,5	11,2	SCG262A263	-	V	E	J	T
	5,6	0,73	12,2	0	3	1,7	2,5	1,3	2,5	1,3	10,5	11,2	SCG262A264	-	V	E	J	T
	7,1	0,82	13,7	0	2	1	1,7	1	1,3	1	10,5	11,2	SCG262A265	-	V	E	J	T
NO - Normally open, NBR seals and UR disc																		
1/4	1,2	0,05	0,8	0	50	35	50	45	50	50	10,5	11,2	SCG262A260	-	-	-	-	T
	2,4	0,17	2,8	0	20	13	20	10	10	9	10,5	11,2	SCG262A261	-	-	-	-	T



OPTIONS

- Valves can also be supplied with FPM (fluoroelastomer), EPDM (ethylene-propylene), CR (chloroprene) and PTFE seals and discs. Use the appropriate optional suffix letter for identification
- Waterproof enclosure with embedded screw terminal coil according to protection class IP67, CEE-10
- Explosionproof enclosures for use in zones 1/21-2/22, categories 2-3 to ATEX Directive 94/9/EC (see "Explosionproof solenoids" section)
- Electrical enclosures according to "NEMA" standards are available
- Compliance with "UL", "CSA" and other local approvals available on request
- Mounting brackets, suffix MB
- Other pipe connections are available on request
- Plug with visual indication and peak voltage suppression or with cable length of 2 m (see Solenoids, Coils & Accessories section)

INSTALLATION

- The solenoid valves can be mounted in any position without affecting operation
- Solenoid valves have 2 mounting holes in body
- Pipe connection identifier is G = G (ISO 228/1)
- Installation/maintenance instructions are included with each valve

SPARE PARTS KIT & ACCESSORIES

catalogue number	spare parts kit no.		mounting bracket no.
	~	=	
SCG262C013/090	C302022	C302068	254573-001
SCG262C019/020/021/022/023	C302018	C302068	-
SCG262A260/261	C302045	C302076	206525-001
SCG262A262/263/264/265	C302051	C302080	254573-001
SCG262D200	C304350	C304350	206525-001
SCG262C202/208/210	C304354	C304354	254573-001
SCG262B212/D232	C304354	C304354	206525-001

(1) Standard prefixes/suffixes are also applicable to kits.
- Not available

ORDERING EXAMPLES:

SC	G	262	C	010	230V / 50 Hz
SC	G	262	C	020	MO 115V / 50 Hz
SC	G	262	C	022	V 24V / DC
SC	G	262	D	200	T 230V / 50 Hz

prefix pipe thread basic number voltage suffix

ORDERING EXAMPLES KITS:

C302045 ⁽¹⁾	
C302051	V
C302051	E

basic number suffix

DIMENSIONS (mm), WEIGHT (kg)



TYPE 01-02

Prefix "SC" Solenoid
Epoxy moulded
IEC 335 / ISO 4400
IP65

Type 01: SCG262C019/020/021/022/023/013/090




Type 02: SCG262D232/C202/C208/C210/B212/D200



TYPE 02

Prefix "SC" Solenoid
Epoxy moulded
IEC 335 / ISO 4400
IP65

SCG262A262/A263/A264/A265/A260/A261



bottom view

① 2 mounting holes Ø M4, depth 6 mm

type	prefix option	A	B	C	D	E	F	G	H	X	weight ⁽²⁾	
											NC	NO
01	SC	75	45	27	40	39	65	75	92	30	0,4	-
02	SC	80	50	30	40	45	69	80	96	30	0,45	0,5

(2) including coil and connector..

All leaflets are available on: www.asconumatics.eu