

646574-1 ☐ SUPERSEDED

Z-PACK | Z-PACK 2mm HM

TE Internal #: 646574-1

TE Internal Description: Z-PACK A/B REC ASY 125P 2MMHM


HM Receptacle Connector: Traditional Backplane, Coplanar, 2mm

[View on TE.com >](#)



Connectors > PCB Connectors > Backplane Connectors > Hard Metric Backplane Connectors >

HM Receptacle Connector: Traditional Backplane, Coplanar, 2mm



PCB Connector Type: **PCB Mount Receptacle**

Data Rate: **≤1 Gb/s**

Number of Columns: **25**

Number of Rows: **5**

Backplane Architecture: **Mezzanine**

[All HM Receptacle Connector: Traditional Backplane, Coplanar, 2mm \(48\)](#)

## Features

### Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Backplane Interface Type	2mm HM
Connector System	Board-to-Board
PCB Connector Type	PCB Mount Receptacle
Sealable	No

### Configuration Features

Rows Loaded	Fully Loaded
Number of Signal Positions	125
Number of Columns	25
Number of Rows	5
Backplane Architecture	Mezzanine
Number of Positions	125
PCB Mount Orientation	Right Angle

### Signal Characteristics

Crosstalk Version	Standard
Data Rate	≤1 Gb/s

### Body Features

Primary Product Color	Gray
-----------------------	------

### Contact Features

Contact Base Material	Phosphor Bronze
-----------------------	-----------------

CompactPCI Designation	None
------------------------	------

PCB Contact Termination Area Plating Material	Tin-Lead
---	----------

Contact Type	Socket
--------------	--------

Contact Mating Area Plating Material	Gold (Au)
--------------------------------------	-----------

Contact Mating Area Plating Material Thickness	.76 $\mu$ m[30 $\mu$ in]
--	--------------------------

Contact Current Rating (Max)	1.5 A
------------------------------	-------

### Termination Features

Termination Method to PCB	Through Hole - Press-Fit
---------------------------	--------------------------

### Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Mating Alignment Type	Polarizing Peg
-----------------------	----------------

### Housing Features

Housing Material	Polyester GF
------------------	--------------

Centerline (Pitch)	2 mm[.078 in]
--------------------	---------------

### Dimensions

Backplane Module Length	49.88 mm
-------------------------	----------

### Operation/Application

Shielded	No
----------	----

Circuit Application	Power & Signal
---------------------	----------------

### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

### Packaging Features

Packaging Quantity	11
--------------------	----

Packaging Method	Tube
------------------	------

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
------------------------------	---------------

EU ELV Directive 2000/53/EC

Not Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025  
(247)

Candidate List Declared Against: JAN 2022  
(223)

SVHC > Threshold:

Pb (13% in Component Part)

**Article Safe Usage Statements:**

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.


Solder Process Capability

Not applicable for solder process capability

**Product Compliance Disclaimer**

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

**Also in the Series | Z-PACK 2mm HM**




Board-to-Board Headers & Receptacles(46)



Connector Contacts(1)



Connector Hardware(91)



Hard Metric Backplane Connectors (264)




Power Contacts(1)




Rectangular Power Connectors(46)

## Customers Also Bought



TE Part #84534-6  
1.25MM FFC POST PLATED V 6P




TE Part #3-338088-3  
8/8 INV.MOD.JACK LOW HALOGEN



TE Part #1241164-5  
2X 5P MOD2A-P STLEI




TE Part #3-1393789-9  
V23079A2011B301



TE Part #7-1571986-2  
A101J1AV2Q004AM marking O -




TE Part #4-1879269-9  
RP 2A 32R4 0.1% 15PPM CUT LENGTH



TE Part #5746443-1  
A/L UNIV HDR 10P ACT PIN LAT



TE Part #6116353-8  
INV MJ,1X2,PNL GRD,LED (YG/YG)



TE Part #6368296-1  
ASSY,SHLD,2X8,STK MJ,WAVE PNL



TE Part #6-147723-9  
20 MODIV VRT SR SFMNT 30AU

## Documents

### Product Drawings

Z-PACK A/B REC ASY 125P 2MMHM

English

### CAD Files

3D PDF

English

Customer View Model

[ENG\\_CVM\\_646574-1\\_B.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_646574-1\\_B.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_646574-1\\_B.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



**Product Specifications**

**Product Specification**

English