

**INSTRUCCIONES DE TRABAJO**Versión n°: 2 Fecha de revisión: Septiembre 2011  
IDT-605: Fichas técnicas de producto**TECHNICAL DATA****One-Wrap® #29****Construction characteristics**

Basic construction

Base material

Width

Overall thickness

Weight

Hooks/cm<sup>2</sup> (type#29)

Colours

Hook colours

**Usage characteristics**

Peel Strength\*

Shear Strength\*

Cycle life \*

Breaking Strength \*

Melting Point

Electric conductivity

Washing resistance

U.V. resistance

Humidity resistance

Sewn resistance

Acid resistance

\* Internal norm of VESA

Extruded and laminated  
Polypropylene & Velour PANominal  $\pm 1\%$  $1.35 \pm 0.30$  mm $550 \pm 60$  g/m<sup>2</sup>

Average 272

White, black, yellow, green, blue and red

Natural. Except for black and white, where the hook is black or white.

Minimum 0.4 N/cm

Minimum 7.0 N/cm<sup>2</sup>

50 % loss after 100 cycles

Minimum 120 N/cm

150°C

None

Good

Low

Medium

Low

Medium

The information included in this Technical Sheet is based on reliable tests and trials. Average value as a reference only, not a nominal specification. Given the diversity of uses of our products we advise our customers to assure themselves that the product meets the requirements of their application. The responsibility for the application and use of the product remains with the customer.

Elaborado: J.C. Lima

Revisado: E. Ducet

Autorizado: J. Jacobs

Fecha: 17.10.11

ANEXO: IDT – 605-B

FTP 601 Versión 2