

HC-26S1N1280DU - Cable connector



1590354

<https://www.phoenixcontact.com/in/products/1590354>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable connector, straight, Screw locking mechanism, M27, number of positions: 26, contact connection type: Socket, shielded: yes, degree of protection: IP67, cable diameter range: 2 mm .. 14.5 mm, number of positions: 26, connection method: Solder connection, series: HC, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1240146

Commercial data

Item number	1590354
Packing unit	12 pc
Minimum order quantity	12 pc
Sales key	ABR
Product key	ABRAJA
GTIN	4046356186995
Weight per piece (including packing)	96.49 g
Weight per piece (excluding packing)	96.49 g
Customs tariff number	85366990
Country of origin	DE

HC-26S1N1280DU - Cable connector



1590354

<https://www.phoenixcontact.com/in/products/1590354>

Technical data

Product properties

Product type	Circular connector (cable-side)
Series	HC
Application	Signal
Number of positions	26
Connection profile	26
Shielded	yes
Coding	N
Thread type	M27

Material specifications

Seal material	FPM or NBR or EPDM
Housing material	Metal
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Insulator material	PA66
Contact material	CuZn
Contact surface	Nickel-plated, gold coating
Gasket and O-ring material	FPM

Connection data

Conductor connection

Connection method	Solder connection
-------------------	-------------------

Electrical properties

Contact

Contact diameter	1 mm
Min. cross section	0.08 mm ²
Max. cross section	1 mm ²
Max. current	8 A
Nominal voltage U _N	48 V AC 74 V DC
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	1.5 kV

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	50
-----------------------------	----

Connector

Type	straight
------	----------

HC-26S1N1280DU - Cable connector



1590354

<https://www.phoenixcontact.com/in/products/1590354>

Direction of rotation	Standard
-----------------------	----------

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M27

Cable/line

External cable diameter	2 mm ... 14.5 mm
-------------------------	------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-20 °C
Altitude	2000 m

HC-26S1N1280DU - Cable connector


1590354

<https://www.phoenixcontact.com/in/products/1590354>




Drawings

Dimensional drawing



Dimensional drawing

Schematic diagram



Connector pin assignment

HC-26S1N1280DU - Cable connector



1590354

<https://www.phoenixcontact.com/in/products/1590354>

Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-26S1N1280DU - Cable connector



1590354

<https://www.phoenixcontact.com/in/products/1590354>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	ad8f818f-bcb8-45d0-86fc-591867d4006f

HC-26S1N1280DU - Cable connector

1590354

<https://www.phoenixcontact.com/in/products/1590354>



Accessories

PROT-M27-SG-IT-IP20 - Plastic protective cap

1577209

<https://www.phoenixcontact.com/in/products/1577209>

Plastic protective cap, M27, series: HC



Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in