




Connectors > Contacts > RF Contacts



RF Contact Style: **Coax**

Contact Type: **Pin**

Number of Positions: **1**

Connector & Contact Terminates To: **Wire & Cable**

Contact Orientation: **Straight**

Features

Product Type Features

RF Contact Style	Coax
Connector & Contact Terminates To	Wire & Cable
Compatible With RF Cable Type	RG 174, RG 188, RG 316

Configuration Features

Number of Positions	1
---------------------	---

Electrical Characteristics

Impedance Options	Non-Matched
-------------------	-------------

Body Features

Shell Plating Material	Gold
Shell Base Material	Brass
	30 µin

Contact Features

	30 µin
Contact Base Material	Beryllium Copper
Contact Type	Pin
Contact Orientation	Straight
Contact Mating Area Plating Material	Gold (Au)
Contact Mating Retention	Without



Contact Current Rating (Max)	1 A
------------------------------	-----

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Method	Carton
------------------	--------

Other

Dielectric Material	PTFE
---------------------	------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (3.7% in 74018819) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts




TE Part # 318813-1
EXTRACTION TOOL ASSY

Customers Also Bought




TE Part #7-1393246-7
W23-X1A1G-7.50=W23/W31



TE Part #1-281838-0
HOUSING HE13 HE14 COSI 10 P




TE Part #1658673-1
HDP-22,PLUG,SIZE 4,62 POSN




TE Part #5-2176389-2
RQ 1206 365R 0.1% 10PPM 5K RL



TE Part #D42180-000
B-155-05




TE Part #1-281695-2
HEADER HE14 STRAIGHT 12 P



TE Part #ZPF000000000202708
DMC-MR 30-23 PN



TE Part #7-1879497-7
CRGH1206 5% 1K5 0.5W



TE Part #6727770001
TMS-SCE-1/2-2.0-0



TE Part #DTS26W11-99SN
PLUG ASSY

Documents

Product Drawings
PIN,STRAIGHT,SIZE 8,AMPLIMITE

English

CAD Files
3D PDF
3D



Customer View Model

[ENG_CVM_CVM_5-228618-1_M.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-228618-1_M.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-228618-1_M.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.