

SELOS WTN · 4 mm² KNIFE DISCONNECT TERMINAL

WTN 4 TKM ...

- Screw connection / mounting on DIN rail TH35
- Nominal cross section 4 mm²
- Screwdriver 0.6x3.5
- Connection capacity: 2 wires, equal size 0.34 – 2.5 mm²



Description	Type	Part No.	Std. Pack
Knife Disconnect Terminal	grey WTN 4 TKM	5D.S04.2055.0	
Knife Disconnect Terminal	red WTN 4 TKM RT	5D.S04.2055.5	
Knife Disconnect Terminal	blue WTN 4 TKM BL	5D.S04.2055.6	

GENERAL DATA		
Width / length / height, incl. TS 7.5	6.1 mm / 40.7 mm / 42.6 mm	
Wire strip length	10 mm	
TECHNICAL DATA	IEC	UL 1059 / CSA 158
	EN 60947-7-1	
Cross section fine-stranded	0.34 - 4 mm ²	
Cross section solid/stranded	0.34 - 6 mm ²	
Cross section, AWG (sol/str)	22-10	
Rated current	32 A	30 A
Rated voltage	400 V	300 V
Rated impulse voltage	6 kV	
Pollution degree	3	

ACCESSORIES	Type	Part No.	Std. Pack
End Plate	grey APWTN 2.5/4	0D.S04.2055.0	

WTN 4 S TKM

- Screw connection / mounting on DIN rail TH35
- Nominal cross section 4 mm²
- Screwdriver 0.6x3.5
- Connection capacity: 2 wires, equal size 0.34 – 2.5 mm²



Description	Type	Part No.	Std. Pack
Knife Disconnect Terminal	grey WTN 4 S TKM	5D.SB4.2055.0	

GENERAL DATA		
Width / length / height, incl. TS 7.5	6.1 mm / 57.8 mm / 42.35 mm	
Wire strip length	10 mm	
TECHNICAL DATA	IEC	UL 1059 / CSA 158
	0.34 - 4 mm ²	
Cross section solid/stranded	0.34 - 4 mm ²	
Cross section, AWG (sol/str)	22-10	
Rated current	32 A	30 A
Rated voltage	800 V	600 V
Rated impulse voltage	8 kV	
Pollution degree	3	

ACCESSORIES	Type	Part No.	Std. Pack
End Plate	grey APWTN 4 S TK...	0D.S04.1955.0	