









## Main

Device short name	MT250
Product or component type	Motor mechanism
Device application	Automatic spring charging
Range compatibility	Compact NSX250 circuit breaker Compact NSX DC circuit breaker PowerPact Multistandard circuit breaker Easypact CVS250 circuit breaker PowerPact J circuit breaker PowerPact H circuit breaker
Control type	Standard
[Uc] control circuit voltage	110...130 V AC 50/60 Hz
Circuit breaker mounting mode	Fixed
Circuit breaker frame rated current	250 A

## Complementary

Control signal type	Impulse Maintained
Response time	< 700 ms (opening) < 80 ms (closing)
Maximum operating frequency	4 per minute
Maximum power consumption in VA	500 VA closing 500 VA opening
Provided equipment	SDE adaptor
Locking options description	Padlocking in OFF position 1 to 3 padlocks Ø 5 to Ø 8

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------