

Technical Data Sheet

Laser/Inkjet Printable Polyester Film

This specification is intended to outline the physical and chemical properties of *PANDUIT*'s pressure sensitive laser and inkjet printable polyester material and include the following part numbers and printable material identifiers:

Part Number Prefixes		
LJSL*Y		

Printable Material Suffixes		
YAJ	YIJ	
YBJ		
YDJ		
YHJ		

PRODUCT SPECIFICATIONS:

Description:	Material is RoHS compliant (European Union directive 2002/95/EC). Material is top coated to provide a laser/inkjet printable surface. This material is intended for indoor use for both laser and inkjet markings. It is also intended for outdoor use for laser printed markings only (inkjet print may be susceptible to fade). This material is halogen free.
Print Methods:	This material is recommended for laser and inkjet printing.
Adhesive:	Acrylic based, pressure sensitive permanent adhesive.
Standard Colors:	Clear with colored print-on area
Thickness:	2.0 +/- 0.3 mils (substrate and adhesive)
Service Temperature Range:	0°F to 275°F (-18°C to 135°C)
Minimum Application Temperature:	50°F (10°C)
Storage Conditions:	Store at 70°F (21°C) and 50% Relative Humidity.

PROPERTIES:**PERFORMANCE:**

Peel Adhesion to Stainless Steel:	35 oz/in width (PSTC-1, 15 min. dwell)										
Shear Adhesion:	24+ hours (PSTC-7, Procedure A)										
Tensile Strength:	MD 56lbs/ inch width +/- 15% (ASTM D882) TD 72 lbs/inch width +/- 15% (ASTM D882)										
Elongation:	MD 160% +/- 15% (ASTM D882) TD 120% +/- 15% (ASTM D882)										
UV Resistance:	3000 hours no change observed (ASTM G53)										
Elevated Temperature Exposure:	After 8 hours at 150°F (65.5°C) there was no deterioration of the substrate										
Tack:	470 g/cm ² (ASTM D-2979-71, 1 sec dwell)										
Immersion Resistance:	Printed samples were applied to stainless steel panels and immersed in "Isopar 'L' and Isopar 'M' solutions to determine if the printing would smear or if the adhesive would degrade.										
	<table> <thead> <tr> <th>Immersion Time</th> <th>Visual Changes</th> </tr> </thead> <tbody> <tr> <td>10 minutes</td> <td>None</td> </tr> <tr> <td>30 minutes</td> <td>None</td> </tr> <tr> <td>60 minutes</td> <td>None</td> </tr> <tr> <td>24 hours</td> <td>None</td> </tr> </tbody> </table>	Immersion Time	Visual Changes	10 minutes	None	30 minutes	None	60 minutes	None	24 hours	None
Immersion Time	Visual Changes										
10 minutes	None										
30 minutes	None										
60 minutes	None										
24 hours	None										

Technical Data Sheet**CHEMICAL/SOLVENT RESISTANCE:**

Samples were laser and inkjet printed. These samples were laminated to flat steel panels and were also wrapped around a 1/12" OD wire. The test was conducted at room temperature after 24 hour dwell. The samples were then immersed in the specified reagents for 5 immersions using the following cycle: a 10 minute immersion time followed by a 30 minute recovery time. After the fifth immersion, the samples were conditioned for 24 hours before testing. Percent retention of performance for samples on flat steel panels was based on a 48 hour adhesion value of 50 oz/inch width.

Chemical Reagent	Visual Observation	Print		Percent Retention of Performance
		Laser	Inkjet	
Distilled Water	No effect	No effect	No effect	98%
Mineral Spirits	No effect	No effect	No effect	96%
Toluene	Slight adhesive bleed	No effect	No effect	91%
Isopropyl alcohol	No effect	No effect	No effect	96%
Methanol	No effect	No effect	No effect	91%
Acetone	Slight adhesive bleed	No effect	No effect	87%
Methyl Ethyl Ketone	Slight adhesive bleed	No effect	No effect	87%
1,1,1 Trichloroethane	No effect	No effect	No effect	94%
Freon TF	No effect	No effect	No effect	87%
Super Agitene	No effect	No effect	No effect	90%
Jet A Fuel	No effect	No effect	No effect	90%
Arco Truslide 68	No effect	No effect	No effect	89%
SAE 30 Motor Oil	No effect	No effect	No effect	102%
10% Nitric Acid	No effect	No effect	No effect	92%

PSTC: Pressure Sensitive Tape Council (U.S.A.)
ASTM: American Society for Testing and Materials (U.S.A.)

Approval

UL Recognized: UL969

File Number: MH14979 (for material suffix YAJ only)

LIMITED WARRANTY

All *PANDUIT* Identification Solution Products (except for Software programs) are warranted to be free from defects in material and workmanship at the time of sale but our obligation under this warranty is limited to replacement of the product proved to be defective within 6 months from the date of sale, or in the case of printers, within 90 days from the date of sale. This warranty is void if the products or printers are modified, altered or misused in any way. Use of *PANDUIT* printers with any product other than the specified *PANDUIT* products for which the printer was designed constitutes misuse. Before using, the user shall determine the suitability of the product for its intended use and user assumes all risk and liability whatsoever in connection therewith. The foregoing may not be altered except by an agreement signed by officers or seller and manufacturer.

NEITHER *PANDUIT* OR SELLER SHALL BE LIABLE FOR ANY OTHER INJURY, LOSS OR DAMAGE, WHETHER DIRECT OR CONSEQUENTIAL, ARISING OUT OF THE USE OF, OR THE INABILITY TO USE THE PRODUCT OR THE PRINTER.

THIS WARRANTY IS MADE IN LIEU OF AND EXCLUDES ALL OTHER WARRANTIES, EXPRESS OR IMPLIED. THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS OF PARTICULAR USE ARE SPECIFICALLY EXCLUDED.

The information contained in this literature is based on our experience to date and is believed to be reliable. It is intended as a guide or use by persons having technical skill at their own discretion and risk. We do not guarantee favorable results or assume any liability in connection with its use. Dimensions contained herein are for reference purposes only. This publication is not to be taken as a license to operate under, or a recommendation to infringe any existing patents. This supersedes and voids all previous literature, etc.