Features

- PID Temperature Controller
- PTC Type Termoresistances Input
- 4 Digits Display
- 10...30Vdc Power Supply
- Selectable Heating or Cooling Function
- Process Output Relay (16A@250Vac)
- Alarm Output Relay (5A@250Vac)

RS PRO PID Temperature Control

RS Stock No:
874065



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Temperature Controller

Product Description

Digital PID and ON/OFF Temperature Control Device
PTC Input type (Scale: -50…150°C / -19,9…99,9°C)
1X Process Output, Relay (16A@250Vac)
1X Alarm Output, Relay (5A@250Vac)
4 Digits display
Applications Fields:
- Machinery Manufacturing
- Panel Manufacturing
- Production and Test Equipment
- Food, Chemical, Textile Sectors
- Industrial Control Applications

General Specifications

Supply Voltage and Power	10…30Vdc
Sensor Inputs	PTC Input type (Scale: -50…150°C / -19,9…99,9°C□)
Output (Process)	1 Relay Output (16(8)A@250Vac) at resistive Load
Output (Alarm)	1 Relay Output (5A@250Vac) at resistive Load
Accuracy	Scale ± %0.25

Mechanical Specifications

Dimension	77 mm x 35 mm 62,5 mm
Panel	IP65 at front, IP20 at rear
Max. Operating Temperature / Humidity	50°C / 90 % max. (None condensing)

Electrical Connection

