



ENGLISH

Datasheet

20m PVC Long Blue Flexible Tube Reinforced

RS Stock number [235-7471](#)



Description:

It is a general purpose hose and is especially suitable for drainage of locations with relatively small differences in elevation; for temporary water supply: for sprinkler irrigation or due to its resistance to most chemicals, for spreading liquid fertilizers and agricultural chemicals.

Light Duty, Blue Lay flat – LH series

Colour: Blue. Operating temperature -25oc / +60oc.

Sizes:

- Available in 100m coils
- 25mm to 207mm ID



Professionally approved products.

Key Features:

- Compact in design
- Made from Cadmium free materials
- Resistant to a wide range of chemicals
- Silicone-free
- Good resistance to abrasion
- Provides good flexibility
- Operating temperature -25oc to +60oc
- Minimum electrical conductivity
- Tough and durability for longer lifespan
- Fast liquid transfer
- Nominal 3 Bar working pressure (light duty)
- Nominal 6 Bar working pressure (medium duty)

Application Examples:

Suitable for drainage, water supply, irrigation and sprinkler systems.

Can also be used for chemical transfer such as liquid fertilisers and other agricultural chemicals.

Specification:

	LH497	LH498	LH499	LH500	LH501	LH502	LH503	LH504
Ex Stock					n/a			
Inner Diameter	25mm	32mm	40mm	52mm	65mm	77mm	103mm	153mm
Tube Material					PVC			
Length					100m Coils			
Maximum Working Pressure					3 Bar			
Working Temperature					-25°C to +60°C			
Weight per meter	n/a	220g	220g	280g	300g	450g	650g	1kg
Weight per coil	n/a	22kg	22kg	28kg	30kg	45kg	65kg	100kg

