




Wire & Cable > Wire & Cable Accessories > Cable Ties



Cable Tie Style: **Standard**
Packaging Method: **Bag**
Tensile Strength: **82 Newton**
Product Length: **98 mm [3.9 in]**

Features

Product Type Features

Cable Tie Style	Standard
Tensile Strength	82 Newton

Body Features

Primary Product Color	Black
Primary Product Material	Polyamide 6.6 GF

Dimensions

Compatible Cable Bundle Diameter Range	21 mm[.82 in]
Product Length	98 mm[3.9 in]
Product Width	2.49 mm[.098 in]
Product Thickness	1 mm[.039 in]

Packaging Features

Packaging Method	Bag
Packaging Quantity	100

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2-160967-1
CABLE TY 98X2.5 NAT

Customers Also Bought

TE Part #3-643817-4
04P MTA156 CONN ASSY 18AWG
ORA

TE Part #917309-1
MINI MLC CONN. TAB CONT.TE Part #150572-2
MINI FASTON 110 REC 20-16 AWG
TPBRTE Part #7-968973-1
AMP MCP 2.8 HSG 15 POS. 2.
LOCKING






TE Part #925015
FF 110 REC HSG 3P NYLON NAT



TE Part #3-643817-6
06P MTA156 CONN ASSY 18AWG ORA




TE Part #9-520272-2
ULTRA-FAST .110/.125 ASY REC 22-18 TPBR



TE Part #735187-2
110 FASTON TAB TPBR



TE Part #925016
4P FF .110 HOUSING REC PA66 NATURAL



TE Part #925014
2 P FF 110(2.8 MM) HOUSING RECEPTACLE

Documents

Product Drawings

CABLE TY 98X2.5 BLA

English

Datasheets & Catalog Pages

Connectivity Solutions for Industrial Applications

English

CABLE TIES

English