**Vishay Semiconductors** 

High Performance Schottky Rectifier, 1 A



www.vishay.com



DO-214AC (SMA)

PRODUCT SUMMARY				
Package	DO-214AC (SMA)			
I <sub>F(AV)</sub>	1 A			
V <sub>R</sub>	100 V			
V <sub>F</sub> at I <sub>F</sub>	0.63 V			
I <sub>RM</sub>	1 mA at 125 °C			
T <sub>J</sub> max.	150 °C			
Diode variation	Single die			
E <sub>AS</sub>	1.0 mJ			

#### **FEATURES**

Low forward voltage drop



FREE

- Guard ring for enhanced ruggedness and long **RoHS** term reliability COMPLIANT HALOGEN
- · Small foot print, surface mountable
- High frequency operation
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

### DESCRIPTION

The VS-10MQ100-M3 surface mount Schottky rectifier has been designed for applications requiring low forward drop and very small foot prints on PC boards. Typical applications are in disk drives, switching power supplies, converters, freewheeling diodes, battery charging, and reverse battery protection.

MAJOR RATINGS AND CHARACTERISTICS					
SYMBOL	CHARACTERISTICS	CHARACTERISTICS VALUES UNITS			
I <sub>F(AV)</sub>	Rectangular waveform	1	А		
V <sub>RRM</sub>		100	V		
I <sub>FSM</sub>	t <sub>p</sub> = 5 μs sine	120	А		
V <sub>F</sub>	1.5 A <sub>pk</sub> , T <sub>J</sub> = 125 °C	0.68	V		
TJ	Range	-55 to +150	°C		

VOLTAGE RATINGS			
PARAMETER	SYMBOL	VS-10MQ100-M3	UNITS
Maximum DC reverse voltage	V <sub>R</sub>	100	N/
Maximum working peak reverse voltage	V <sub>RWM</sub>		

ABSOLUTE MAXIMUM RATINGS					
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS
Maximum average forward current		50 % duty cycle at $T_L = 126$ °C On PC board 9 mm <sup>2</sup> island (0.013 mm thick copper pad are		1.5	
See fig. 4	IF(AV)	$I_{F(AV)}$ 50 % duty cycle at $T_L = 135$ °C, rectangu On PC board 9 mm <sup>2</sup> island (0.013 mm thick copper pad area)		1	A
Maximum peak one cycle non-repetitive surge current, $T_1 = 25 \ ^{\circ}C$		5 µs sine or 3 µs rect. pulse	Following any rated load condition and with	120	
See fig. 6	I <sub>FSM</sub>	10 ms sine or 6 ms rect. pulse		30	
Non-repetitive avalanche energy	E <sub>AS</sub>	T <sub>J</sub> = 25 °C, I <sub>AS</sub> = 0.5 A, L = 8 mH		1.0	mJ
Repetitive avalanche current	I <sub>AR</sub>	$\begin{array}{c} \mbox{Current decaying linearly to zero in 1 } \mu \mbox{s} \\ \mbox{Frequency limited by } T_J \mbox{ maximum } V_A = 1.5 \mbox{ x } V_R \mbox{ typical} \end{array} \begin{array}{c} 0.5 \end{array}$		0.5	А

Revision: 20-Jan-15 Document Number: 93365 1 For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishav.com/doc?91000



www.vishay.com

# Vishay Semiconductors

ELECTRICAL SPECIFICATIONS					
PARAMETER	SYMBOL	TEST CONDITIONS		VALUES	UNITS
		1 A	T <sub>.1</sub> = 25 °C	0.78	V
Maximum forward voltage drop	V <sub>FM</sub> <sup>(1)</sup>	1.5 A	1j=23 0	0.85	
See fig. 1	V FM (1)	1 A	– T <sub>.1</sub> = 125 °C	0.63	
		1.5 A	$I_{\rm J} = 125  {}^{\circ}{\rm C}$	0.68	
Maximum reverse leakage current		T <sub>J</sub> = 25 °C		0.1	mA
See fig. 2	I <sub>RM</sub>	$V_{\rm R} = \text{Rated } V_{\rm R}$	$v_{\rm R} = Raled v_{\rm R}$	1	mA
Threshold voltage	V <sub>F(TO)</sub>	$T_{\rm J} = T_{\rm J} \text{ maximum} \qquad \qquad$		0.52	V
Forward slope resistance	r <sub>t</sub>			mΩ	
Typical junction capacitance	CT	$V_R = 10 V_{DC}$ , $T_J = 25 \text{ °C}$ , test signal = 1 MHz 38		pF	
Typical series inductance	L <sub>S</sub>	Measured lead to lead 5 mm from package body 2.0		nH	
Maximum voltage rate of change	dV/dt	Rated V <sub>R</sub> 10 000 V/µs		V/µs	

#### Note

<sup>(1)</sup> Pulse width = 300  $\mu$ s, duty cycle = 2 %

THERMAL - MECHANICAL SPECIFICATIONS				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum junction and storage temperature range	T <sub>J</sub> <sup>(1)</sup> , T <sub>Stg</sub>		-55 to +150	°C
Maximum thermal resistance, junction to ambient	R <sub>thJA</sub>	DC operation	80	°C/W
Approvimete weight			0.07	g
Approximate weight			0.002	oz.
Marking device		Case style SMA (similar D-64)	1,	J

#### Note

(1)  $\frac{dP_{tot}}{dT_J} < \frac{1}{R_{thJA}}$  thermal runaway condition for a diode on its own heatsink








Fig. 1 - Maximum Forward Voltage Drop Characteristics








Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage

## **Vishay Semiconductors**




Fig. 6 - Maximum Peak Surge Forward Current vs. Pulse Duration

#### Note

<sup>(1)</sup> Formula used:  $T_C = T_J - (Pd + Pd_{REV}) \times R_{thJC}$ ;

Pd = Forward power loss = I<sub>F(AV)</sub> x V<sub>FM</sub> at (I<sub>F(AV)</sub>/D) (see fig. 6); Pd<sub>REV</sub> = Inverse power loss = V<sub>R1</sub> x I<sub>R</sub> (1 - D); I<sub>R</sub> at V<sub>R1</sub> = 80 % rated V<sub>R</sub>

Revision: 20-Jan-15

3

Document Number: 93365


For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>

# VS-10MQ100-M3





### **ORDERING INFORMATION TABLE**



-M3 = halogen-free, RoHS-compliant and terminations lead (Pb)-free

ORDERING INFORMATION (Example)					
PREFERRED P/N	PREFERRED PACKAGE CODE	MINIMUM ORDER QUANTITY	PACKAGING DESCRIPTION		
VS-10MQ100-M3/5AT	5AT	7500	13" diameter plastic tape and reel		

LINKS TO RELATED DOCUMENTS			
Dimensions www.vishay.com/doc?95400			
Part marking information	www.vishay.com/doc?95403		
Packaging information	www.vishay.com/doc?95404		



# **Outline Dimensions**

# **Vishay Semiconductors**

SMA

## **DIMENSIONS** in inches (millimeters)

DO-214AC (SMA)





Vishay

# Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.