




Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Plug**
Number of Positions: **1**
Terminal Orientation: **Straight**
UL Flammability Rating: **UL 94V-2**

Features

Product Type Features

Connector & Contact Terminates To	Wire & Cable
Sealable	No
Connector System	Wire-to-Wire
Connector & Housing Type	Plug

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	With

Mechanical Attachment

--



Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon 66
------------------	----------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 172864-1 250 POSITIVE DBL LOCK 2P NATUR	 TE Part # 170452-1 PL 250 AM REC 22-20 AWG 0.406 X 21 BR	 TE Part # 172863-1 250 POSITIVE DBL LOCK 1P	 TE Part # 170454-1 PL 250 AUTOMOTIVE REC 18-14 0.40 X 21 BR
 TE Part # 170456-1 PL 250 AUTOMOTIVE REC 12-10 0.40 X 21 BR	 TE Part # 170452-2 PL 250 AUTOMOTIVE REC 22-20 AWG PRE TPBR	 TE Part # 170456-2 PL 250 AM REC 12-10 0.40 X 21 PRE-TPBR	 TE Part # 170454-2 PL 250 AM REC 18-14 0.40 X 21 PRE-TPBR

Also in the Series | Positive Lock 250

 Automotive Terminals(1)	 Crimp Terminal Housings(177)	 Insertion & Extraction Tools(3)	 Insulation Boots & Sleeves(5)
 Quick Disconnects(173)			

Customers Also Bought





TE Part #1743757-2
SPT SEALED 3P CAP HSG




TE Part #965927-2
SPLICE F.DRAHT+FFC



TE Part #1612122-1
SQUIB LOCKING BUTTON



TE Part #2005281-3
MT3/JPT/SPT HYB 58P PLUG ASSY



TE Part #1-2005275-3
MT3/JPT/SPT HYB 58P CAP ASSY



TE Part #CAT-EC7491-CH8172
ECONOSEAL, CONNECTOR HOUSING



TE Part #85011-1
RUBBER PLUG FOR SEALED CONN.



TE Part #CP4904-000
ES2000-NO.1-C1-0-65MM-SH



TE Part #1897214-1
MCP 6.3 2P PLUG ASSY

Documents

Product Drawings
PL .250 (6.3 MM) HOUSING

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_174090-2_G_c-174090-2-g.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_174090-2_G_c-174090-2-g.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_174090-2_G_c-174090-2-g.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Crimping of 250 Series, Automotive Positive Lock Receptacle Contact

English

Application Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English

Instruction Sheet (non U.S.)

Japanese