

Product information

92 91 02

Precision Cross Jaw Tweezers




- Hold automatically: Their spring force makes these holding tweezers perfect for soldering small and very small components, among other uses
- For applications that require a high-precision self-closing function, for example in microscopy or for precision assembly or soldering tasks
- For soldering work on transistors, gold wire diodes, etc.
- Suitable for a wide variety of applications in the electronics industry thanks to perfectly symmetrical tips and excellent balance
- The high quality stainless steel ensures extreme toughness and very good corrosion resistance against a variety of atmospheric environments and many corrosive materials
- Only variants made of premium stainless steel: handcrafted, with an excellent matt, scratch-free and non-reflective surface
- Variants made from premium stainless steel only: precision cross-over tweezers for particularly challenging applications when corrosion resistance and toughness are the main requirements
- The high-quality premium stainless steel versions offer high temperature resistance and excellent corrosion resistance to most chemicals, salts and acids
- Premium stainless steel

General

Article No.	92 91 02
EAN	4003773086819
Material	premium stainless steel
Gripping surfaces	smooth gripping surfaces
Weight	12 g
Dimensions	120 x 10 x 11 mm
Reach-konform	no
RohS-konform	no

Technical details

Surface	matt finish
Finish	straight
Tips width (A)	0.12 mm
Tips width (B)	0.2 mm
Tweezers tip version	needle-point
Corrosion-resistant	yes
ESD-tested	no
VDE tested	no
Sectors	Industry electronics
Magnetic	non-magnetisable (80%)



Classification	
eCl@ss 5.1.4	21040500
ETIM 5.0	EC000182
ETIM 6.0	EC000182
proficl@ss 6.0	EAB696c019

technical change and errors excepted