

## Features

- Prevents unintended overloading for safe lifting.
- Dynamic proof load tested at 1.5 x WLL; automatic load reaction brake with double safety (two brake pawls, four brake springs).
- Compact design with sprocket wheel and drive shaft supported by needle and slide bearings.
- Swivel Hooks with Safety Latches – Easy in-line positioning; hooks open under overload instead of breaking.
- All-steel body with powder-coated finish and plated frame components.
- Temperature Range – Operates from -10°C to +50°C.
- CE-marked, UKCA-marked, EN 13157, EN 818-7; safety factor 4:1.

## RS PRO Lever Hoist with Overload Protection, 3200 kg Load Capacity, 1.5m Lift

RS Stock No.: 0712615



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

*The RS PRO Lever Hoist with Overload Protection is designed for safe, efficient, and reliable lifting in demanding industrial environments. Featuring a factory-integrated overload protection device, this hoist ensures controlled lifting and prevents accidental overloading. Its robust steel construction, precision bearings, and corrosion-resistant load chain deliver smooth operation and long-term durability. With compliance to EN 13157 and EN 818-7 standards, this lever hoist offers superior safety and performance for professional applications.*

## General Specifications

<b>Load Capacity (WLL)</b>	3200 kg
<b>Lift Height</b>	1.5 m
<b>Overload Protection</b>	Yes
<b>Material</b>	All-steel construction
<b>Finish</b>	Powder-coated, plated frame components
<b>Temperature Range</b>	-10°C to +50°C
<b>Safety Factor</b>	4:1

## Approvals

<b>Standards Met</b>	EN 13157, EN 818-7, CE-marked, UKCA-marked
<b>Chain Standard</b>	EN 818-7 T(8), electro-galvanized

## Similar Products

Stock No.	Brand	Product Name	Load Capacity	Lift Height	Overload Protection
0712607	RS PRO	Lever Hoist	250 kg	1.5 m	-
0712608	RS PRO	Chain Block	2000 kg	3.0 m	Yes
0712609	RS PRO	Chain Block	500 kg	3.0 m	Yes
0712610	RS PRO	Lever Hoist	1600 kg	1.5 m	Yes
0712611	RS PRO	Lever Hoist	800 kg	1.5 m	Yes
0712612	RS PRO	Chain Block	1000 kg	3.0 m	Yes
0712613	RS PRO	Push Trolley	1000 kg	Fits I-Beams	-
0712614	RS PRO	Lever Hoist	500 kg	1.5 m	Yes
0712615	RS PRO	Lever Hoist	3200 kg	1.5 m	Yes
0712616	RS PRO	Lifting Magnet	Lifting Capacity: 600 kg	-	-