

S460 - Hi-Vis Winter Traffic Jacket

Collection: 300D Industry High Visibility

Range: High Visibility

Shell Fabric: 300D Industry: 100% Polyester, 300D Oxford, Stain Resistant Finish, Double PU Coated, 190g

Outer Carton: 12

Product information

This fully certified waterproof jacket is a popular option across many industries. Hard-wearing, functional and packed full of features including a drawstring hood, studded storm flap and multiple storage pockets.

300D Industry High Visibility

A comprehensive range of single and combination garments in a highly durable, EN343 certified fabric including some new cleverly designed and innovative styles.

High Visibility

Our extensive range of High-Visibility clothing meets stringent requirements in both design and construction, to ensure compliance with the latest EN ISO 20471 & ANSI standards. Innovative and technical, our High Visibility range is ideal for those who will not compromise on style, comfort, protection and performance.

Standards

EN ISO 20471 Class 3
RIS 3279 TOM Issue 2 (Orange Only)
EN 343 Class 3:1 X (WP 15,000mm)
EN 342 (0.345 (M².K/W), 2, X)
ANSI/ISEA 107 Type R Class 3
ANSI/ISEA 107 TYPE P Class 3
AS 4602.1:2024 Class D/N



Features

- Waterproof with taped seams preventing water penetration
- Extremely water resistant PFAS free Texpel™ Splash Eco fabric finish, water beads away from fabric surface
- EN342 Protection against cold certified up to -36°C
- Inner ribbed cuffs for warmth and comfort
- Hook and loop cuffs for a secure fit
- Two lower pockets
- Internal chest pocket
- Quilt lined for thermal insulation
- Storm flap front to protect against the elements
- Reflective tape for increased visibility
- Two-way zip for quick and easy access

S460 - Hi-Vis Winter Traffic Jacket

Commodity Code: 6210200010

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
 Bracetown Business Park
 D15 YN2P, Ireland
 Cert No: 2777/12749-04/E00-00

SATRA Technology Centre Ltd (Notified Body No.: AB: 0321)
 SATRA Technology Park
 NN16 8SD, United Kingdom
 Cert No: AB0321/17282-01/E00-00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
S460ORRXS	Orange	65.0	45.0	40.0	1.0200	0.1170	5036108022816	25036108760538
S460ORRS	Orange	65.0	45.0	40.0	0.9600	0.1170	5036108022823	25036108760514
S460ORRM	Orange	65.0	45.0	40.0	1.1200	0.1170	5036108022830	25036108760507
S460ORRL	Orange	65.0	45.0	40.0	1.1400	0.1170	5036108022847	25036108760491
S460ORRXL	Orange	65.0	45.0	44.0	0.9200	0.1287	5036108022854	25036108760521
S460ORRXXL	Orange	65.0	45.0	44.0	1.2000	0.1287	5036108022861	25036108760545
S460ORRXXXL	Orange	65.0	45.0	44.0	1.2700	0.1287	5036108022878	25036108760552
S460ORR4XL	Orange	65.0	45.0	50.0	1.3200	0.1463	5036108043378	25036108760477
S460ORR5XL	Orange	65.0	45.0	50.0	1.3600	0.1463	5036108043385	25036108760484
S460ORR6XL	Orange	65.0	45.0	50.0	1.4400	0.1463	5036108347872	25036108836493