



STRIPPING DIMENSION

**1.0 ELECTRICAL**

- 1.1 FREQUENCY RANGE: DC-1 GHz
- 1.2 NOMINAL IMPEDANCE: 75 OHMS
- 1.3 VOLTAGE RATING: 500 VOLTS MAX.

**2.0 MATERIALS**

- 2.1 BODIES: BRASS PER JIS-C3604
- 2.2 CENTER CONTACT: BRASS PER JIS-2680

**3.0 FINISHES AND OTHERS**

- 3.1 SEE BELOW TABLE FOR DETAILS.

**4.0 MECHANICAL**

- 4.1 FOR USE WITH RG59U OR SIMILAR STYLE CABLE
- 4.2 CABLE ATTACHMENT: OUTER: TWIST ON, INNER: PLUG IN

**5.0 ENVIRONMENTAL**

- 5.1 OPERATING TEMPERATURE RANGE: -20° C TO +60° C

9	INSULATION	POM	1	NONE
8	CENTER CONTACT	BRASS	1	GOLD
7	BODY	BRASS	1	NICKEL 100μ" MIN.
6	WASHER	BRASS	1	NICKEL
5	SPRING WASHER	SK-5	1	NICKEL
4	WASHER	BRASS	1	NICKEL
3	GASKET	RUBBER	1	RED
2	INSULATION	POM	1	NONE
1	SHELL	ZINC	1	NICKEL
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH

APPROVED

by \_\_\_\_\_ DATE: \_\_\_\_\_



DESCRIPTION		BNC STRAIGHT PLUG TWIST-ON									
製圖	DRAWN	TOLERANCE		品名	13-17-1	D.G.Z	59U	日期	DATE	版次	REV.
	Kristina	X	±0.2	TITLE	\ROHS COMPLIANT (75Ω)			01.05.15'		A-0	
檢圖	CHECK	XX	±0.1	單位	mm(in)	DWG.NO.	13-0416				
	Arc			比例	SCALE						
認定	APPROVAL	XXX	±0.05	比例	SCALE						
	Angela	ANGLE	±5°	比例	4:1						