


Data sheet

chainflex® CF130.UL



Control cable (Class 4.4.1.2) • For medium duty applications • PVC outer jacket • Flame retardant



1. Outer jacket: Pressure extruded, gusset-filling PVC mixture
2. CFRIP: Tear strip for faster cable stripping
3. Core insulation: Mechanically high-quality TPE mixture
4. Conductor: Fine-wire strand consisting of bare copper wires
5. Strain relief: Tensile stress-resistant centre element
6. 12 cores or more: Bundles with optimised pitch length and pitch direction

Example image
For detailed overview please see design table

Cable structure

	Conductor	Finely stranded conductor consisting of bare copper wires (following DIN EN 60228).
	Core insulation	Mechanically high-quality TPE mixture.
	Core structure	Number of cores < 12: Cores wound in a layer with short pitch length. Number of cores ≥ 12: Cores wound in bundles which are then wound around a high tensile strength centre element, all with optimised short pitch lengths and directions. Especially low-torsion structure.
	Core identification	Cores < 0.5 mm²: Colour code in accordance with DIN 47100. Cores ≥ 0.5 mm²: Black cores with white numbers, one green-yellow core.
	Outer jacket	Low-adhesion PVC mixture, adapted to suit the requirements in e-chains® (following DIN EN 50363-4-1). Colour: Silver-grey (similar to RAL 7001) Printing: black
	CFRIP®	Strip cables faster: a tear strip is moulded into the outer jacket Video ▶ www.igus.eu/CFRIP

„00000 m*** igus chainflex CF130.---.UL① -----② ---/---V③ E310776

cRUus AWM Style 20200 VW-1 AWM I/II A/B 60°C 300V FT1 EAC/CTP

CE RoHS-II conform www.igus.de +++ chainflex cable works +++

* **Length printing:** Not calibrated. Only intended as an orientation aid.
① / ② Cable identification according to Part No. (see technical table).
③ Printing of nominal voltage (see general electrical values).
Example: ... chainflex ... CF130.02.30.UL ... 30x0.25 ... 300 V/500 V ...



Data sheet







chainflex® CF130.UL



Control cable (Class 4.4.1.2) • For medium duty applications • PVC outer jacket • Flame retardant



Dynamic information

	Bend radius	e-chain® linear flexible fixed	minimum 7.5 x d minimum 6 x d minimum 4 x d
	Temperature	e-chain® linear flexible fixed	+5 °C up to +70 °C -5 °C up to +70 °C (following DIN EN 60811-504) -15 °C up to +70 °C (following DIN EN 50305)
	v max.	unsupported gliding	3 m/s 2 m/s
	a max.		20 m/s ²
	Travel distance		Unsupported travels and up to 50 m for gliding applications, Class 4
	Torsion		± 90°, with 1 m cable length, Class 2



These values are based on specific applications or tests. They do not represent the limit of what is technically feasible.

Guaranteed service life according to guarantee conditions

Double strokes	5 million		7.5 million		10 million	
	< 10 m	≥ 10 m	< 10 m	≥ 10 m	< 10 m	≥ 10 m
Temperature, from/to [°C]	R min. [factor x d]	R min. [factor x d]	R min. [factor x d]	R min. [factor x d]	R min. [factor x d]	R min. [factor x d]
+5/+15	10	12.5	11	13.5	12	14.5
+15/+60	7.5	10	8.5	11	9.5	12
+60/+70	10	12.5	11	13.5	12	14.5

Minimum guaranteed service life of the cable under the specified conditions.
The installation of the cable is recommended within the middle temperature range.

Electrical information

	Nominal voltage	300/500 V (following DIN VDE 0298-3)
	Testing voltage	2000 V (following DIN EN 50395)



Example image

igus® chainflex® CF130.UL

Data sheet

chainflex® CF130.UL



Control cable (Class 4.4.1.2) ● For medium duty applications ● PVC outer jacket ● Flame retardant




Properties and approvals

	Flame retardant	According to IEC 60332-1-2, CEI 20-35, FT1, VW-1
	Silicone-free	Free from silicone which can affect paint adhesion (following PV 3.10.7 – status 1992)
	UL/CSA	Style 10493 and 20200, 300 V, 60 °C
	NFA	Following NFPA 79-2012, chapter 12.9
	EAC	Certificate No. RU C-DE.ME77.B.01254 (TR ZU)
	CTP	Certificate No. C-DE.PB49.B.00416 (Fire protection)
	CEI	Following CEI 20-35
	Lead-free	Following 2011/65/EC (RoHS-II)
	Clean room	According to ISO Class 1, material/cable tested by IPA according to DIN EN ISO standard 14644-1
	CE	Following 2014/35/EU

Typical lab test setup for this cable series

Test bend radius R	approx. 38 - 200 mm
Test travel S	approx. 1 - 15 m
Test duration	minimum 2 - 4 million double strokes
Test speed	approx. 0.5 - 2 m / s
Test acceleration	approx. 0.5 - 1.5 m / s ²



Data sheet

chainflex® CF130.UL



Control cable (Class 4.4.1.2) ● For medium duty applications ● PVC outer jacket ● Flame retardant



Example image

Typical application areas

- For medium duty applications, Class 4
- Unsupported travel distances and up to 50 m for gliding applications, Class 4
- Without influence of oil, Class 1
- Torsion $\pm 90^\circ$, with 1 m cable length, Class 2
- Preferably indoor applications
- Wood/stone processing, Packaging industry, supply systems, Handling, adjusting equipment



Data sheet

chainflex® CF130.UL



Control cable (Class 4.4.1.2) ● For medium duty applications ● PVC outer jacket ● Flame retardant



Technical tables:

Mechanical information

Part No.	Number of cores and conductor nominal cross section [mm²]	Outer diameter (d) max. [mm]	Copper index [kg/km]	Weight [kg/km]
CF130.02.03.UL	3x0.25	5.0	8	24
CF130.02.04.UL	4x0.25	5.5	11	29
CF130.02.06.UL	6x0.25	6.0	16	48
CF130.02.07.UL	7x0.25	6.5	19	56
CF130.02.12.UL	12x0.25	8.5	33	96
CF130.02.20.UL	20x0.25	10.5	51	145
CF130.02.25.UL	25x0.25	11.5	66	154
CF130.02.30.UL	30x0.25	12.5	75	184
CF130.03.02.UL	2x0.34	5.0	8	25
CF130.03.05.UL	5x0.34	6.0	18	40
CF130.05.02.UL	2x0.5	5.5	11	38
CF130.05.03.UL	3G0.5	5.5	16	39
CF130.05.04.UL	4G0.5	6.0	21	47
CF130.05.05.UL	5G0.5	6.5	26	55
CF130.05.07.UL	7G0.5	7.5	37	76
CF130.05.12.UL	12G0.5	10.0	63	139
CF130.05.18.UL	18G0.5	12.0	94	183
CF130.05.25.UL	25G0.5	13.5	129	259
CF130.07.02.UL	2x0.75	6.0	15	41
CF130.07.03.UL	3G0.75	6.0	23	49
CF130.07.04.UL	4G0.75	6.5	30	58
CF130.07.05.UL	5G0.75	7.0	38	68
CF130.07.07.UL	7G0.75	8.0	53	95
CF130.07.12.UL	12G0.75	11.0	90	152
CF130.07.18.UL	18G0.75	13.5	134	226
CF130.07.25.UL	25G0.75	16.0	186	342
CF130.07.36.UL	36G0.75	19.0	293	531
CF130.07.42.UL	42G0.75	21.0	341	608
CF130.10.02.UL	2x1.0	6.0	20	51
CF130.10.03.UL	3G1.0	6.5	30	60
CF130.10.04.UL	4G1.0	7.0	40	74
CF130.10.05.UL	5G1.0	7.5	50	89
CF130.10.07.UL	7G1.0	9.0	70	121
CF130.10.12.UL	12G1.0	12.5	119	197
CF130.10.18.UL	18G1.0	15.0	178	278
CF130.10.25.UL	25G1.0	17.5	248	395

Note: The given outer diameters are maximum values and may tend toward lower tolerance limits.
G = with green-yellow earth core x = without earth core



Data sheet

chainflex® CF130.UL



Control cable (Class 4.4.1.2) ● For medium duty applications ● PVC outer jacket ● Flame retardant



Part No.	Number of cores and conductor nominal cross section [mm ²]	Outer diameter (d) max. [mm]	Copper index [kg/km]	Weight [kg/km]
CF130.15.02.UL	2x1.5	7.0	30	62
CF130.15.03.UL	3G1.5	7.0	45	77
CF130.15.04.UL	4G1.5	8.0	60	97
CF130.15.05.UL	5G1.5	8.5	75	115
CF130.15.07.UL ¹⁷⁾	7G1.5	9.5	104	153
CF130.15.12.UL	12G1.5	13.0	178	275
CF130.15.18.UL	18G1.5	17.5	267	466
CF130.15.25.UL	25G1.5	19.5	371	592
CF130.15.36.UL	36G1.5	23.5	579	887
CF130.15.42.UL ¹¹⁾	42G1.5	26.5	729	1084
CF130.25.03.UL	3G2.5	8.5	75	118
CF130.25.04.UL	4G2.5	9.5	100	147
CF130.25.07.UL ¹⁷⁾	7G2.5	12.0	174	249
CF130.25.12.UL	12G2.5	17.5	297	510
CF130.40.03.UL	3G4.0	10.0	119	187
CF130.40.05.UL	5G4.0	12.0	198	299
CF130.60.04.UL	4G6.0	13.5	238	371
CF130.60.05.UL	5G6.0	14.5	299	471

¹⁷⁾ When using the cables with "7 G 1.5 mm²" and "7 G 2.5 mm²" minimum bend radius must be 17.5 x d with gliding travel distance ≥ 5 m.

¹¹⁾ Phase-out model

Note: The given outer diameters are maximum values and may tend toward lower tolerance limits.
G = with green-yellow earth core x = without earth core



Data sheet

chainflex® CF130.UL



Control cable (Class 4.4.1.2) ● For medium duty applications ● PVC outer jacket ● Flame retardant



Electrical information

Conductor nominal cross section [mm ²]	Maximum conductor resistance at 20 °C (following DIN EN 50289-1-2) [Ω/km]	Maximum current rating at 30 °C (following DIN VDE 0298-4) [A]
0.25	79.0	5
0.34	57.0	7
0.5	39.0	10
0.75	26.0	14
1	19.5	17
1.5	13.3	21
2.5	8.0	30
4	4.95	41
6	3.3	53

The final maximum current rating depends among other things on the ambient conditions, the type of the installation and the number of loaded cores.



Data sheet

chainflex® CF130.UL



Control cable (Class 4.4.1.2) • For medium duty applications • PVC outer jacket • Flame retardant

Design table

Part No.	Number of cores	Core design	Part No.	Number of cores	Core design
CF130.XX.02.UL	2		CF130.XX.18.UL	6x3	
CF130.XX.03.UL	3		CF130.XX.20.UL	5x4	
CF130.XX.04.UL	4		CF130.XX.25.UL	5x5	
CF130.XX.05.UL	5		CF130.XX.30.UL	6x5	
CF130.XX.06.UL	6		CF130.XX.36.UL	6x6	
CF130.XX.07.UL	7		CF130.XX.42.UL	7x6	
CF130.XX.12.UL	4x3				

Example image
igus® chainflex® CF130.UL



Data sheet

chainflex® CF130.UL



Control cable (Class 4.4.1.2) ● For medium duty applications ● PVC outer jacket ● Flame retardant

Colour code in accordance with DIN 47100.

Conductor no.	Colours according to DIN ISO 47100	Conductor no.	Colours according to DIN ISO 47100	Conductor no.	Colours according to DIN ISO 47100
1	white	22	brown-blue	43	blue-black
2	brown	23	white-red	44	red-black
3	green	24	brown-red	45	white-brown-black
4	yellow	25	white-black	46	yellow-green-black
5	grey	26	brown-black	47	grey-pink-black
6	pink	27	grey-green	48	red-blue-black
7	blue	28	yellow-grey	49	white-green-black
8	red	29	pink-green	50	brown-green-black
9	black	30	yellow-pink	51	white-yellow-black
10	violet	31	green-blue	52	yellow-brown-black
11	grey-pink	32	yellow-blue	53	white-grey-black
12	red-blue	33	green-red	54	grey-brown-black
13	white-green	34	yellow-red	55	white-pink-black
14	brown-green	35	green-black	56	pink-brown-black
15	white-yellow	36	yellow-black	57	white-blue-black
16	brown-yellow	37	grey-blue	58	brown-blue-black
17	white-grey	38	pink-blue	59	white-red-black
18	brown-grey	39	grey-red	60	brown-red-black
19	white-pink	40	pink-red	61	black-white
20	white-brown	41	grey-black		
21	white-blue	42	pink-black		



Example image

igus® chainflex® CF130.UL

