



PRODUCT DATASHEET

Datasheet creation date: 2025/05/28 10:43 (UTC)

MOTION & CONTROL
NSK



23124CE4

Spherical Roller Bearings


Boundary Dimensions

d	120	mm	Bore diameter
D	200	mm	Outside diameter
B	62	mm	Width
r (min.)	2	mm	Chamfer dimension

Basic Load Ratings

Cr	580000	N	Basic dynamic load rating
C0r	720000	N	Basic static load rating

Speeds




Thermal Speed Rating (Oil-bath)	2800	min-1	Oil-bath lubrication subject to conditions outlined in ISO 15312
Mechanical (forced-circulation oil)	3600	min-1	Properly designed and controlled forced-circulation oil lubrication

Abutment and Fillet Dimensions

da (min.)	130	mm	Diameter of shaft abutment
da (max.)	138	mm	Diameter of shaft abutment
Da (min.)	175	mm	Diameter of housing abutment
Da (max.)	190	mm	Diameter of housing abutment
ra (max.)	2	mm	Radius of shaft or housing fillet

Calculation factors



e	0.29	Constant
Y2	3.5	Axial load Factors
Y3	2.4	Axial load Factors
Y0	2.3	Axial load Factors

Mass

Mass approx.	7.85	kg	Mass approx.
--------------	------	----	--------------