




Connectors > Rectangular Connectors > Standard Rectangular Connectors > STD Temp Sig GRACE INERTIA Plug



Connector Product Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Board**

UL Flammability Rating: **UL 94V-0**

Number of Positions: **4**

[All STD Temp Sig GRACE INERTIA Plug \(63\)](#)

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Rows	1

Electrical Characteristics

Operating Voltage	50 VAC
-------------------	--------

Body Features

Primary Product Color	Natural
-----------------------	---------



Contact Features

Contact Layout	Inline
Contact Type	Socket

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Housing Material	Nylon 66 GF
Centerline (Pitch)	2 mm [.079 in]

Dimensions

Connector Width	6.75 mm [.266 in]
Connector Height	7.9 mm [.311 in]
Connector Length	9.54 mm [.375 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C [-22 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Halogen Free	No
Circuit Application	Signal

Identification Marking

Circuit Identification Feature	Without
--------------------------------	---------

Industry Standards

Compatible With Agency/Standards Products	UL
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Package
Packaging Quantity	400

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 1903393-1
GIC 2.5 W CAP HSG 4P NATURAL



TE Part # CAT-G7534A-P729
STD Temp Sig GRACE INERTIA Plug




TE Part # 3-1903393-4
GIC 2.5 W CAP HSG 4P YELLOW



TE Part # 2400014-4
GIC2.0 EV CAP HOUSING 4 POS. NATURAL



TE Part # 2367943-4
GI2.0EV VT SMT Poting HDR,NTL,Key A,4P



TE Part # 1-1903393-2
GIC 2.5 W CAP HSG 4P RED

Also in the Series | GRACE INERTIA 2.0




Connector Contacts(4)



PCB Headers & Receptacles(70)



Rectangular Connector Housings(20)



Standard Rectangular Connectors(38)



Wire-to-Board Connector Assemblies & Housings(1)



Wire-to-Board Headers & Receptacles (70)


Customers Also Bought



TE Part #1-1879214-9
CPF 0402 499R 0.1% 25PPM 1K RL




TE Part #NB42782001
RNF-100-3/16-4-STK



TE Part #1971032-4
4POS HEADER ASSEMBLY FOR GIC 2.0 EV



TE Part #4-640427-1
11P MTA156 CONN ASSY 20AWG YEL



TE Part #281810-1
JUNIOR TIMER WIRE SEAL CO



TE Part #2307383-3
1POS,FAKRA AUT,SOC HSG ASSY, SLD,180 DEG




TE Part #1437565-2
FSM100=12MM,TACTILE,PB SWITCH



TE Part #2-456134-2
CRIMPER, INSULATION "F"(.110")



TE Part #2040113-1
0.50/1.0/2.8 SEALED LEVER 114POS



TE Part #1-174656-1
E-J MK-2 PLUG HSG 10P NATURAL

Documents



Product Drawings

4POS Plug housing for GIC 2.0 EV Series

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1971030-4_F_c-1971030-4-f.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1971030-4_F_c-1971030-4-f.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1971030-4_F_c-1971030-4-f.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English