Disclaimer. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



FRONT PLATE NSX/CVS 250 HORIZONTAL FIXED ROTARY HANDLE W850 4M

LVS03301

EAN Code: 3606481871978

Main

Range	PrismaSeT	
Range of product	PrismaSeT G	
Product or component type	Front plate	
Accessory / separate part category	Installation accessory	
Range compatibility	PrismaSeT PrismaSeT G enclosure	
Type of front plate	Cut-out	
Installed device	EasyPact: fixed CVS100160 without earth leakage protection - control: direct front rotary handle - horizontal installation EasyPact: fixed CVS250 without earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX100160 without earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX250 without earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX100160 integrated earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX250 integrated earth leakage protection - control: direct front rotary handle - horizontal installation Human-switchboard interface: 96 x 96 mm device Human-switchboard interface: HSI Enerlin'X: fixed FDM121 - control: remote control - vertical installation	
Poles description	1 x 3P: mounting plate support: CVS100160 horizontal installation 1 x 4P: mounting plate support: CVS100160 horizontal installation 1 x 3P: mounting plate support: CVS250 horizontal installation 1 x 4P: mounting plate support: CVS250 horizontal installation 1 x 3P: mounting plate support: NSX100160 horizontal installation 1 x 4P: mounting plate support: NSX100160 horizontal installation 1 x 3P: mounting plate support: NSX250 horizontal installation 1 x 4P: mounting plate support: NSX250 horizontal installation	
Operating position	Horizontal	

Complementary

Enclosure/cubicle description	Floor-standing enclosure - width 850 mm	
Connection position	Direct connection	
Number of vertical modules [50 mm]	4	
Standards	IEC 61439-2 IEC 61439-1	
Product certifications	ASTA	
Surface finish	Textured Matt	
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder	
Colour	White (RAL 9003)	

Life Is On Schneider 1 Jul 2025

Height	200 mm 750 mm	
Width		
Quantity per set	Set of 1	
functional unit	850 mm PrismaSeT G floor-standing enclosure human-switchboard interface 96 x 96 mm device 1 4 850 mm PrismaSeT G floor-standing enclosure human-switchboard interface HSI 1 4 850 mm PrismaSeT G floor-standing enclosure Enerlin'X FDM121 fixed remote control vertical 1 4 850 mm PrismaSeT G floor-standing enclosure EasyPact CVS100160 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 850 mm PrismaSeT G floor-standing enclosure EasyPact CVS100160 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 850 mm PrismaSeT G floor-standing enclosure EasyPact CVS250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 850 mm PrismaSeT G floor-standing enclosure EasyPact CVS250 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 850 mm PrismaSeT G floor-standing enclosure ComPact NSX100160 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 850 mm PrismaSeT G floor-standing enclosure ComPact NSX100160 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 850 mm PrismaSeT G floor-standing enclosure ComPact NSX250 without fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 850 mm PrismaSeT G floor-standing enclosure ComPact NSX250 without fixed direct front rotary handle horizontal 4P 1 direct with long terminal shield 4 850 mm PrismaSeT G floor-standing enclosure ComPact NSX250 without fixed fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 850 mm PrismaSeT G floor-standing enclosure ComPact NSX100160 integrated fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4 850 mm PrismaSeT G floor-standing enclosure ComPact NSX250 integrated fixed direct front rotary handle horizontal 3P 1 direct with long terminal shield 4	

Environment

IP degree of protection IP30

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	20.0 cm
Package 1 Length	75.0 cm
Package 1 Weight	1.445 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	10.5 cm
Package 2 Width	22.0 cm
Package 2 Length	76.0 cm
Package 2 Weight	8.937 kg
Unit Type of Package 3	P12
Number of Units in Package 3	60
Package 3 Height	35.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	101.0 kg

Logistical informations

Country of origin

FR

Contractual warranty

Warranty

1 Jul 2025

18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better


Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
Halogen content performance	Halogen free plastic parts product
PVC free	Yes

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No

Technical Illustration

Dimensions



All dimensions are approximate and are in r
 Also see technical documentation.