

# Eaton 134489

Catalog Number: 134489

Eaton SPX Variable frequency drive, 400 V AC, 3-phase, 90 kW, IP21, Radio interference suppression filter, Brake chopper, OLED display, FR8



### General specifications

Product Name	Catalog Number
Eaton SPX variable frequency drive	134489
EAN	Product Length/Depth
4015081313389	758 mm
Product Height	Product Width
344 mm	291 mm
Product Weight	Certifications
58 kg	Certified by UL for use in Canada
	RoHS, ISO 9001
	DNV
	UL 508C
	Safety: EN 61800-5-1: 2003
	UL
	Specification for general requirements:
	IEC/EN 61800-2
	CUL
	CSA-C22.2 No. 14
	UL File No.: E134360
	CE
	IEC/EN61800-5
	CSA Class No.: 3211-06
	UL Category Control No.: NMMS,
	NMMS2, NMMS7, NMMS8
	UL report applies to both US and
	Canada
	IEC/EN 61800-3
	RCM
	IEC/EN61800-3

## General

### Degree of protection

IP21

NEMA Other

### Electromagnetic compatibility

1st and 2nd environments (according to EN 61800-3)

### Fitted with:

Brake chopper

IGBT inverter

Internal DC link

OLED display

DC link choke

Radio interference suppression filter

### Frame size

FR8

### Mounting position

Vertical

### Product Category

Variable frequency drives

### Protection

Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4)

### Radio interference class

C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary.

### Suitable for

Branch circuits, (UL/CSA)

## Climatic environmental conditions

### Altitude

Max. 3000 m

Max. 1000 m

Above 1000 m with 1 % performance reduction per 100 m

### Ambient operating temperature - min

-10 °C

### Ambient operating temperature - max

50 °C

### Ambient operating temperature at 150% overload - min

-10 °C

### Ambient operating temperature at 150% overload - max

50 °C

### Ambient storage temperature - min

-40 °C

### Climatic proofing

< 95 % relative humidity, no condensation, no corrosion, no dripping water

## Main circuit

### Mains voltage - min

380 V

### Mains voltage - max

500 V

### Operating mode

Sensorless vector control (SLV)

Optional: Vector control with feedback (CLV)

U/f control

### Output frequency - min

0 Hz

### Output frequency - max

320 Hz

### Output voltage (U<sub>2</sub>)

400 V AC, 3-phase

500 V AC, 3-phase

480 V AC, 3-phase

### Rated control supply voltage

10 V DC (Us, max. 10 mA)

#### Rated frequency - min

45 Hz

#### Rated frequency - max

66 Hz

#### Rated operational current (Ie) at 110% overload

205 A

#### Rated operational current (Ie) at 150% overload

170 A

#### Rated operational power at 380/400 V, 50 Hz

90 kW

#### Rated operational power at 380/400 V, 50 Hz, 110% overload

110 kW

#### Rated operational voltage

400 V AC, 3-phase

480 V AC, 3-phase

500 V AC, 3-phase

#### Resolution

0.01 Hz (Frequency resolution, setpoint value)

#### Supply frequency

50/60 Hz

#### Switching frequency

3.6 kHz, 1 - 10 kHz adjustable, fPWM, Power section, Main circuit

#### System configuration type

AC supply systems with earthed center point

#### Voltage rating - max

480 VAC

## Communication

#### Communication interface

BACnet/IP, optional

LonWorks, optional

DeviceNet, optional

Modbus-TCP, optional

PROFIBUS-DP

## Motor rating

Assigned motor current IM at 400 V, 50 Hz, 110% overload

196 A

Assigned motor current IM at 400 V, 50 Hz, 150% overload

161 A

Assigned motor current IM at 440 - 480 V, 60 Hz, 150% overload

156 A

Assigned motor current IM at 440/480 V, 60 Hz, 110% overload

180 A

Assigned motor power at 460/480 V, 60 Hz

125 HP

Assigned motor power at 460/480 V, 60 Hz, 110% overload

150 HP

## Control circuit

Number of inputs (analog)

2 (parameterizable, 0 - 10 V DC, 0/4 - 20 mA)

Number of inputs (digital)

6 (parameterizable, max. 30 V DC)

Number of outputs (analog)

1

Number of outputs (digital)

1 (parameterizable, 48 V DC/50 mA)

Number of relay outputs

2 (parameterizable, N/O, 8 A (24 V DC) / 8 A (250 V AC) / 0,4 A (125 V DC))

Rated control voltage (Uc)

24 V DC (external, max. 250 mA)

## Design verification

Equipment heat dissipation, current-dependent Pvid

2250 W

Rated operational current for specified heat dissipation (In)

170 A

10.2.2 Corrosion resistance

CANopen®, optional  
BACnet MS/TP, optional  
EtherCAT, optional  
Ethernet IP, optional  
Modbus-RTU, optional  
PROFINET, optional

Connection to SmartWire-DT

No

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

10.10 Temperature rise

The panel builder is responsible for the temperature rise

calculation. Eaton will provide heat dissipation data for the devices.

#### 10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

#### 10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

#### 10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

## Resources

### Application notes

[SPI - Variable frequency drives with a common DC bus](#)

[Connecting drives to generator supplies](#)

[Electromagnetic compatibility \(EMC\)](#)

### Catalogs

[Product Range Catalog Drives Engineering](#)

### Declarations of conformity

[DA-DC-00004868.pdf](#)

[DA-DC-00004869.pdf](#)

### Drawings

[eaton-frequency-inverter-dimensions-007.eps](#)

### Installation instructions

[IL04020008Z](#)

### Multimedia

[Eaton variable frequency drives - Demand more expertise](#)

[Eaton variable frequency drives - Demand more innovation](#)

[Eaton variable frequency drives - Demand more than good enough](#)

[How does a VFD work to save energy and money?](#)

### Product notifications

[eaton-drives-ecodesign-directive-mz040046en-en.pdf](#)