




Hydrostatic submersible pressure transmitter

SUBMERSIBLE 0,25BAR 10M FEP CABLE



Product characteristics

Number of inputs and outputs	Number of analogue outputs: 1				
Measuring range	0...0.25 bar	0...250 mbar	0...3.63 psi	0...100.4 inH ₂ O	0...25 kPa

Application

Design	with capillary tube for pressure compensation		
Application	for industrial applications		
Media	Liquids		
Medium temperature [°C]	-10...85		
Min. bursting pressure	2.4 bar	35 psi	240 kPa
Pressure rating	2 bar	29 psi	200 kPa
Type of pressure	relative pressure		

Electrical data

Operating voltage [V]	10...30 DC			
Protection class	III			
Reverse polarity protection	yes			
Measuring principle	hydrostatic			

Inputs / outputs

Number of inputs and outputs	Number of analogue outputs: 1				
------------------------------	-------------------------------	--	--	--	--

Outputs

Total number of outputs	1			
Output signal	analogue signal			
Number of analogue outputs	1			
Analogue current output [mA]	4...20			
Max. load [Ω]	700; (U _b = 24 V; (U _b - 10 V) / 20 mA)			
Short-circuit protection	yes			

Measuring/setting range

Measuring range	0...0.25 bar	0...250 mbar	0...3.63 psi	0...100.4 inH ₂ O	0...25 kPa
-----------------	--------------	--------------	--------------	------------------------------	------------

Accuracy / deviations

Repeatability [% of the span]	< 0,1; (with temperature fluctuations < 10 K)			
Characteristics deviation [% of the span]	< 0,25 (BFSL) / 0,5; (incl. linearity, zero and span error (limit value setting))			
Linearity deviation [% of the span]	< 0,2 (BFSL)			
Long-term stability [% of the span]	< 0,2; (per year)			



Hydrostatic submersible pressure transmitter

SUBMERSIBLE 0,25BAR 10M FEP CABLE

Temperature coefficient zero point [% of the span / 10 K]	$< \pm 0,2; (0...50\text{ }^{\circ}\text{C})$
Temperature coefficient span [% of the span / 10 K]	$< \pm 0,2; (0...50\text{ }^{\circ}\text{C})$

Operating conditions

Ambient temperature [°C]	-10...85
Storage temperature [°C]	-30...80
Protection	IP 68

Tests / approvals

MTTF [years]	403
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request

Mechanical data

Weight [g]	991.5
Housing	cylindrical
Dimensions [mm]	Ø 27 / L = 147
Materials	stainless steel (316Ti/1.4571); PA


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 10 m, FEP, Ø 7.5 mm

Connection



1: screen (connected to the housing)
Core colours :
BN = brown
GN = green