

Inline terminal - IB IL 24 PWR IN-PAC - 2861331

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Inline power terminal, complete with accessories (connector plug and labeling field), 24 V DC, without fuse




The illustration shows the version IB IL 24 PWR IN/F-PAC

Why buy this product

- Supply of the 24 V main voltage UM
- Provision of the 24 V segment voltage US
- Main circuit protected by an external fuse
- Diagnostic and status indicators



Key commercial data

Packing unit	1 pc
GTIN	 4 017918 894276
Weight per Piece (excluding packing)	77.3 g
Custom tariff number	85389091
Country of origin	Germany

Technical data

Note:

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	12.2 mm
Height	119.8 mm
Depth	71.5 mm

Interfaces

Connection method	Inline data jumper
Interface	Inline local bus

Inline terminal - IB IL 24 PWR IN-PAC - 2861331

Technical data

Power supply

Communications power U_L	7.5 V DC (via voltage jumper)
----------------------------	-------------------------------

General

Type of protection	Surge protection
Protective circuit/component	Suppressor diode
Weight	59 g
Number of connectors	1

Inline potentials

Communications power U_L	7.5 V DC $\pm 5\%$ (via voltage jumper)
Main circuit supply U_M	24 V DC (nominal value)
Supply voltage range U_M	19.2 V ... 30 V (including all tolerances, including ripple)
Power supply at U_M	max. 8 A (Sum of $U_M + U_S$; 4 A, maximum, when used in potentially explosive areas.)
Segment supply voltage U_S	24 V DC
Power supply at U_S	max. 8 A (Sum of $U_M + U_S$; 4 A, maximum, when used in potentially explosive areas.)

Classifications

eCl@ss

eCl@ss 4.0	27250315
eCl@ss 4.1	27250304
eCl@ss 5.0	27250304
eCl@ss 5.1	27242610
eCl@ss 6.0	27242610
eCl@ss 7.0	27242610
eCl@ss 8.0	27242610

ETIM

ETIM 2.0	EC001433
ETIM 3.0	EC001600
ETIM 4.0	EC001600
ETIM 5.0	EC001600

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

Inline terminal - IB IL 24 PWR IN-PAC - 2861331

Approvals

Approvals

Approvals


UL Recognized / cUL Recognized / GOST / LR / GL / BV / DNV / ABS / RINA / GL-SW / BSH / BSH / cULus Recognized / GL


Ex Approvals

UL Listed / cUL Listed / ATEX / cULus Listed

Approvals submitted

Approval details

UL Recognized 

cUL Recognized 

GOST 

LR

GL

BV

DNV

ABS

RINA


GL-SW

Inline terminal - IB IL 24 PWR IN-PAC - 2861331

Approvals

BSH

BSH

cULus Recognized 

GL

Accessories

Accessories

Labeling panel

Labeling field - IB IL FIELD 2 - 2727501

Labeling field, width: 12.2 mm



Plug

Inline plug - IB IL SCN-PWR IN-CP - 2727637



Connector, colored, for Inline power and segment terminal blocks

Inline plug - IB IL SCN-PWR IN - 2727462

Connector, for Inline power and segment terminal blocks



Terminal marking

Inline terminal - IB IL 24 PWR IN-PAC - 2861331

Accessories


Insert strip - ESL 62X10 - 0809492

Insert strip, Sheet, white, Unlabeled, Can be labeled with: Office printing systems, Plotter: Laser printer, Mounting type: Insert, Lettering field: 62 x 10 mm




Drawings

Block diagram



Internal wiring of the terminal points

Connection diagram



Dimensioned drawing

