


FEATURES

- Fix input unregulated dual output
- Continuous short-circuit protection.
- Industry standard pin-out
- I/O isolation test voltage 1.5KVDC
- No-load input current as low as 5mA
- Operating temperature range
 40°C to +105°C
- High efficiency up to 85%
- IEC62368, UL62368, EN62368 approved

RS PRO 1W isolated DC-DC converters

• 2233635, 2233636, 2233638, 2233641, 2233642



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

PCB Mount DC-DC converters are specially designed for applications where isolated voltage is required in a distributed power supply system. They are suitable for: pure digital circuits, low frequency analog circuits, relay-driven circuits and data switching circuits. Featuring continuous short circuit protection and no-load input current as low as 8Ma

General Specifications

Model	DC-DC 1W Isolated DC-DC converter	
Mounting Type	Type PCB	
MTBF	MIL-HDBK-217F@25°C > 3,500,000 hrs	
Applications Industrial control systems, instrumentation, analogue, relay-driven and data switching circuits.		

20.01	Input Voltage (Vdc)		Output	Output		Max. Capacitive Load(μF)	Efficiency (Typ)
RS Stock#	Nominal	Max	Voltage Current	Wattage			
2233635	·		±3.3V	±152/±15mA	1W	1200	74%
2233636		5V		±100/±10mA	1W	1200	82%
2233638	5V (4.5-5.5)			±42/±5mA	1W	220	83%
2233641	(4.3 3.3)		±15V	±34/±4mA	1W	220	83%
2233642			±24V	±21/±3mA	1W	100	85%

Input Specifications

Input Specification					
Item	Operating Conditions	Min.	Тур.	Max.	Unit
no-ioad)	3.3VDC/5VDC output	-	270/5	286/10	
	12VDC output		241/12	254/20	mA
	15VDC/24VDC output	-	241/18	254/30	
Reflected Ripple Current	Nominal input voltage	-	15	-	
Surge Voltage (1sec. max.)	5VDC input	-0.7	-	9	VDC
Input Filter		Capacitance Filter			
Hot Plug		Unavailable			



Output Specifications

Output Specification						
Item	Operating Condit	Operating Conditions		Тур.	Max	Unit
Voltage Accuracy			See ou	tput regula	ntion curves	(Fig. 1)
Linear Regulation	Input voltage	3.3VDC output	-	-	±1.5	%
Linear Regulation	change: ±1%	Other outputs	-	-	±1.2	
	10% -100% load	3.3VDC output	-	15	20	
		5VDC output		10	15	
Load Regulation		12VDC output		7	10	
		15VDC output		6	10	
		24VDC output	-	5	10	
Temperature Coefficient	100% load		-	±0.02	-	%/°C
Ripple & Noise *	20MHz bandwidth	3.3VDC/5VDC & 12VDC outputs	-	30	75	mV p-p
		24VDC output		50	100	
Short circuit Protection				ontinuous,	self-recover	γ


Note: * The "parallel cable" method is used for ripple and noise test, please refer to DC-DC Converter Application Notes for specific information.

General Specifications

Item	Operating Condition	Operating Conditions			Max.	Unit
Isolation	Input-output Electri minute with a leaka max.	1500	-	-	VDC	
Insulation Resistance	Input-output resista	nce at 500VDC	1000	-	-	МΩ
Isolation Capacitance	Input-output capaci 100KHz/0.1V	Input-output capacitance at 100KHz/0.1V		20		pF
Operating Temperature	Derating when operating temperature≥85°C, (see Fig. 2)		-40	-	+105	
Storage Temperature		<u> </u>	-55	-	+125	°C
Casa Tamananatuna Diaa	Ta=25°C	3.3VDC output	-	25	-	
Case Temperature Rise		Others	-	15	-	
Storage Humidity	Non-condensing		-	-	95	%RH
Pin Soldering Resistance Temperature	Soldering spot is 1.5mm away from case for 10 seconds		-	-	300	°C
Switching Frequency *	Full load, nominal input voltage		-	270	-	KHz
MTBF	MIL-HDBK-217F@2	5°C		3500		K hours



Typical Performance Curves









Fig. 1









Design Reference

Typical application

Input and/or output ripple can be further reduced, by connecting a filter capacitor from the input and/or output terminals to ground as shown in Fig.3. Choosing suitable filter capacitor values is very important for a smooth operation of the modules, particularly to avoid start-up problems caused by capacitor values that are too high. For recommended input and output capacitor values refer




Table 1: Recommended input and output capacitor values

Vin	Cin	Vout	Cout
5VDC	4.7μF	±3.3VDC	4.7μF
		±5VDC	4.7μF
		±12VDC	1μF
		±15VDC	0.47μF
		±24VDC	0.47μF

EMC (Class B) compliance circuit




Table 2 : EMC recommended circuit value table

	Output voltage (VDC)		3.3/5VDC	12/15/24VDC	
		C1/C2	4.7μF /25V	4.7μF /25V	
la a contra		СУ		1nF/4KVDC VISHAY	
Input	EMI		-	HGZ102MBP TDK CD45-	
voltage 5VDC	EIVII			E2GA102M-GKA	
SVDC	C3	C3/C4	Refer to the C	Cout in table 1	
		LDM	6.8μH	6.8μH	




EMC Specifications


Emissions CE CISPR32/EN55032 CLASS B (see Fig. 4 for recommended circuit) RE CISPR32/EN55032 CLASS B (see Fig. 4 for recommended circuit)		CISPR32/EN55032 CLASS B (see Fig. 4 for recommended circuit)			
		ircuit)			
Immunity	ESD	EC/EN61000-4-2 Air ±8kV , Contact ±4kV Perf. Criteria B			
Note: Refer to Fig.4 for recommended circuit test					

Mechanical Specifications

Case material	Black plastic; flame-retardant and heat-resistant (UL94 V-0)
Dimensions	19.65 x 6.00 x 10.16mm
Weight	2.1g (Typ.)
Cooling Method	Free air convection


Dimensions and recommended layout





Pi	Pin-Out		
PIN	Dual		
1	Vin		
2	GND		
4	-Vo		
5	0V		
6	+Vo		

Note: Grid 2.54*2.54mm





Approvals

Safety Certification IE

IEC62368, UL62368, EN62368 approved

- 1. If the product is not operated within the required load range, the product performance cannot be guaranteed to comply with all parameters in the datasheet.
- 2. The maximum capacitive load offered were tested at input voltage range and full load.
- 3. Unless otherwise specified, parameters in this datasheet were measured under the conditions of Ta=25°C, humidity
- 4. Our products shall be classified according to ISO14001 and related environmental laws and regulations.