

Enamelled copper wire on mini bobbin  
**CUL 100/0,10**



## Advantages

Insulating varnish basis min. polyurethane, mod. current loading

Degree 1

TJ min. 155 °C

Solderable

## Applications

Enamelled copper wire for the production of coils and winding and for general laboratory needs.

## Approvals



## Enamelled copper wire on mini bobbin **CUL 100/0,10**

Type	CUL 100/0,10	Type	CUL 100/0,10
Electrical data		<b>Operating data</b>	
		current car. cap.	0.03 A
		<b>Environment</b>	
		Heat resistance	155 °C (CL.F)
		insulating varnish	min. Polyurethan, mod.
		Tin-plate	>350 °C
		<b>Measures and weights</b>	
		Wire diameter	0.10 mm
		Weight	0.10 kg
		Length m (min.)	1144

30  
Mechanical data

Subjects to change.