



## GBC 250HS Office A3 Laminator

The GBC 250HS A3 Laminator provides a reliable and efficient solution for everyday office laminating needs. Designed for professional environments, this high-speed laminating machine combines performance with ease of use. Boost productivity and reduce lamination time by 30% using GBC high-speed pouches. With a rapid 1-minute warm-up time, it laminates a 75-micron A4 sheet in just 36 seconds, making it ideal for fast-paced office tasks. The intuitive control panel offers three pouch thickness settings from 75 to 125 microns, providing flexibility for various document types. The panel also features an anti-jam reverse button for smooth removal of misfed pouches. Additionally, the SMART status LED system provides clear visual and audible cues: red during warm-up, blue with a sound when ready, and an automatic shut-off after 15 minutes of inactivity to conserve energy. The SMART entry guide LEDs ensure straight pouch alignment to prevent jams, making every lamination perfect. Protect and preserve your important documents with speed and a smooth, professional finish every time. Black and red colour.



## Attributes

- Rapid warm-up time, ready to use in just 1 minute.
- Compatible with pouches from 75 to 125 microns. Laminates ID card up to A3 sized documents.
- GBC High-Speed laminators reduce lamination time by 30% when using GBC high-speed pouches.
- Laminates an A4 document (75 mic) in just 36 seconds.
- Laminates 16 x A4 in 10 minutes.
- SMART status LED: glows red during warm-up and turns blue with an acoustic signal when the laminator is ready to use.
- SMART entry guide LEDs: ensure pouches feed straight through the laminator to prevent jams.
- The control panel features an anti-jam reverse button for easy removal of misfed pouches.
- Includes a starter pack of 5x A4 pouches (75 microns).
- Conserve energy with the 15-minute auto shut-off feature, which activates after detecting inactivity.
- Low noise level <50DbA for less distractions.
- For best results use with GBC document pouches. CE certified, TUV/GS.

## Specifications

Number	4410071UK
Colour	
Material	ABS Plastic
Dimensions (W x H x D)	500 x 92 x 180 mm
Laminating Speed (mm/min)	500
Temperature	125C-136C
Power Supply	220-240V AC 50/60Hz
Warm up Time (min)	1
Heating System	2 from outside heated rollers
Operation Mode	2 roller, no carrier, temperature controlled
Max. Laminating Width (mm)	330
Max. Laminating Thickness (mm)	0.5
Max. Pouch Thickness (microns)	75-125
Power Consumption (W)	1400
Dimensions (with Tray) mm	500 x 92 x 180
Anti-Jam Technology	Manual reverse button
Approx. lamination time (A4)	36 secs (A4 80 micron)
Photo friendly	Yes
Period of Warranty (Years)	2
Type	Pouch
Weight	2640 g
Pallet quantity	0
EAN code	5028252645584