

PRODUCT-DETAILS

Sentry TSR20

Sentry TSR20 Safety relay



General Information

| | |
|-----------------------|---------------------------|
| Extended Product Type | Sentry TSR20 |
| Product ID | 2TLA010061R0000 |
| EAN | 7350024483352 |
| Catalog Description | Sentry TSR20 Safety relay |

| | |
|------------------|---|
| Long Description | Sentry TSR20 Safety relay with delayed relay outputs 3NO+1NC, +24VDC power supply and screw terminals. For monitoring of safety devices with contacts, 1 or 2 equivalent channels, and safety devices with OSSD outputs. OFF-delay time (0,5s or 1,5s) selectable by switch on the front. |
| | Sentry safety relays cover various types of safety applications up to PLe / SIL3. Basic models provide reliable supervision of simpler safety functions, while universal models provide advanced features and high flexibility. Models with display offer preset configurations and extensive information to further simplify troubleshooting. Additional variants offer a high accuracy timer function of $\pm 1\%$ and an adjustable time setting range from 0-999 s. High output current capacity of up to 6 A can save the use of an intermediary contactor. Multi-reset allows up to 10 safety relays connected to one reset light-button. All models are available with detachable push-in or screw terminals. Terminals and coding kit to mark removed terminals are available as accessories. |

Ordering

| | |
|------------------------|--|
| Minimum Order Quantity | 1 piece |
| Customs Tariff Number | 85364900 |
| Product Main Type | TSR |
| Product Name | Safety relay |
| Function | Safety relay for monitoring of safety devices |
| Sub-Function | Start/test input, Auto reset only, Time delay selectable by switch |

Special FunctionsTime delay selectable by switch. Auto reset only.

Popular Downloads

| | |
|-----------------------------------|------------------------------------|
| Data Sheet, Technical Information | 2TLC010037L0201 |
| Instructions and Manuals | 2TLC010070M0201 |
| Dimension Diagram | 2TLC010001U0201 |
| Wiring Diagram | 2TLC010014T0001 |
| CAD Dimensional Drawing | 2CDC001079B0201 |
| Marketing Video | 2TLC010019N0201 2TLC010018N0201 |

Dimensions

| | |
|----------------------------|----------|
| Product Net Depth / Length | 120 mm |
| Product Net Height | 120 mm |
| Product Net Width | 22.5 mm |
| Product Net Weight | 0.207 kg |

Safety Information

| | |
|------------------------------|---|
| Certification Agency | cULus TÜV SÜD CE CCC RCM S UKCA KC |
| Performance Level (PL) | Up to e |
| Safety Integrity Level (SIL) | 3 |

Technical

| | |
|--|------------------------------|
| Number of Outputs | Failsafe, Delayed Contacts 4 |
| Rated Control Supply Voltage (U _s) | 24 V DC |
| Time Range | 0.5 and 1.5 seconds |

Environmental

| | |
|-------------------------|--|
| Ambient Air Temperature | Operation -25 ... +65 °C Storage -40 ... +70 °C |
| Degree of Protection | IP20 |
| | 10% ... 90%; no icing; occasional condensation |

Certificates and Declarations (Document Number)

| | |
|----------------------------------|---------------------|
| CQC Certificate | CQC2017010303977544 |
| cUL Certificate | 2TLC010006D0201 |
| cULus Certificate | 2TLC010007D0201 |
| Declaration of Conformity - CCC | 2020980303000244 |
| Declaration of Conformity - CE | 2TLC010010D0201 |
| Declaration of Conformity - UKCA | 2TLC010190D0201 |
| Instructions and Manuals | 2TLC010070M0201 |
| KC Certificate | 2TLC010048D0201 |

| | |
|------------------|-----------------|
| RoHS Information | 2TLC010010D0201 |
| TÜV Certificate | 2TLC010008D0201 |

Container Information

| | |
|--------------------------------|---------------|
| Package Level 1 Units | box 1 piece |
| Package Level 1 Width | 125 mm |
| Package Level 1 Depth / Length | 31 mm |
| Package Level 1 Height | 129 mm |
| Package Level 1 Gross Weight | 0.268 kg |
| Package Level 1 EAN | 7350024483352 |

Classifications

| | |
|------------------------------------|---|
| eClass | V11.0 : 27371819 |
| ETIM 7 | EC001449 - Device for monitoring of safety-related circuits |
| ETIM 8 | EC001449 - Device for monitoring of safety-related circuits |
| ETIM 9 | EC001449 - Device for monitoring of safety-related circuits |
| IDEA Granular Category Code (IGCC) | 5367 >> Control relay |
| UNSPSC | 39122331 |
| Object Classification Code | K |
| E-Number (Finland) | 2712529 |
| E-Number (Sweden) | 3860826 |

Categories

Low Voltage Products and Systems → Control Products → Electronic Relays and Controls → Safety Relays → Expansion Relays
Low Voltage Products and Systems → Control Products → Safety Products → Safety Relays → Expansion Relays

