

### Main

Range	Multi9
Product name	Multi9 PRD1
Product or component type	Surge arrester
Device short name	PRD1 75r
Poles description	2P
Remote signalling	With
Signal contacts composition	1 SD (1 C/O)
Surge arrester type	Electrical distribution network





### Complementary

Surge arrester class type	Type 1
Surge arrester technology	MOV
Wiring configuration	3-wire
Nominal discharge current	Common mode: 20 kA (L/PE)
Maximum discharge current	75 kA
[Iimp] impulse current	75 kA
[Uc] maximum continuous operating voltage	Common mode: 175 V AC L/N Differential mode: 350 V AC L/L
Maximum [Up] voltage protection level	<600 V L/N <1200 V L/L
Disconnecter device type	Associated circuit breaker 30 A curve C 14 kA
Short-circuit withstand	200 kA
Local signalling	Green mechanical indicator for operating Red mechanical indicator for end of life
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	4
Height	91.7 mm
Width	35 mm
Depth	71.4 mm
Net weight	340 g
Colour	Grey (RAL 7035)
Response time	< 25 ns
Connections - terminals	Tunnel type terminal 6...35 mm <sup>2</sup> (AWG 10...AWG 2) - rigid Tunnel type terminal 6...25 mm <sup>2</sup> (AWG 10...AWG 4) - flexible Tunnel type terminal (dry contacts) 0.5...1.5 mm <sup>2</sup>
Wire stripping length	10 Mm for L/N connection 10 Mm for PE connection 6 mm for dry contacts connection
Tightening torque	3 N.M L/N 3 N.m PE

## Environment

Standards	UL 1449:ed. 4
IP degree of protection	NEMA 1 built-in:
Pollution degree	3
Relative humidity	0...95 %
Operating altitude	2000 m
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

## Offer Sustainability

REACH Regulation	<a href="#"> REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#"> EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
China RoHS Regulation	<a href="#"> China RoHS Declaration</a>
RoHS exemption information	<a href="#"> Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins